robern®

M SERIES ARCH DOOR CABINET

WITH ELECTRIC, DEFOGGER, AND NIGHT LIGHT

MP20D4ABRL

ALSO MP20D4ABLL, MP20D4APRL, MP20D4APLL

Features

- *Recess or surface mount*
- *Mirrored doors and interior, matte silver interior*
- *3-way adjustable concealed hinge system*
- *SAFESEAL™ gasket frame*
- *Patented swing-out magnifying mirror*
- *Rust-free aluminum construction*
- *Left or right hinge door available*
- *Four adjustable glass shelves*
- *Electric feature includes two duplex 15 A, 110 VAC GFCI outlets and mirror defogger*
- *Night light concealed in the finger pull of the door provides soft ambient light*
- *Light sensor automatically turns night light on at lower light levels and can be overridden by a switch*
- *19-1/4″ (48.9 cm) x 43-3/8″ (110.2 cm) x 4-5/8″ (11.7 cm)*



Codes/Standards Applicable

Specified model meets or exceeds the following:

- *Electrical options are UL listed for damp locations*

Specified Model

Model	Description	
MP20D4ABRL	Beveled edge, right-hand, electric with night light and defogger	❑
MP20D4ABLL	Beveled edge, left-hand, electric with night light and defogger	❑
MP20D4APRL	Plain edge, right-hand, electric with night light and defogger	❑
MP20D4APLL	Plain edge, left-hand, electric with night light and defogger	❑
NOTE: Hardware required for installing cabinets side-by-side is included.		

Required Accessories - For Surface-Mount Installations Only		
MPSK40D4	Beveled mirror side kit	❑
MPSK40D4P	Plain mirror side kit	❑
M40SKD4A	Aluminum side kit	❑
Refer to the Price Guide for additional side kit colors and finishes		

Required Accessories - For Multiple Cabinets Installed or Stacked Vertically Only		
MSF___S	Stack filler for surface-mounted cabinet installations	❑
MSF___R	Stack filler for recessed cabinet installations	❑
MSF___D2	Stack filler for partially recessed cabinet installations	❑
Follow MSF with width of full cabinet array plus any installed lights when ordering. For example, MSF **49.5** S is stack filler for two surface-mounted 24″ (61 cm) cabinets and one kit of 1-1/2″ (3.8 cm) lights [23-1/4″ (59.1 cm) + 23-1/4″ (59.1 cm) + 1-1/2″ (3.8 cm) + 1-1/2″ (3.8 cm)].		

Optional Accessories		
SLB20D4	Safety-lock box	❑
Frames, light options, and additional accessories are also available. Refer to the Price Guide for more information.		

USA: 1-800-877-2376
www.robern.com

M SERIES ARCH DOOR CABINET

Technical Information

Roughing-in opening	18-1/2″ (47 cm) x 38-5/8″ (98.1 cm) x 4″ (10.2 cm)
Door opening angle	170°

Installation Notes

Install this product according to the installation guide.

When determining the height of the mirrored cabinet, ensure the mirrored door will clear all obstacles, such as a faucet. A minimum distance of 1” (2.5 cm) is required.

Secure the screws (provided) to a stud to avoid possible property and product damage. If this is not possible, anchors (provided) must be inserted before installing the screws.

Modular components can be joined horizontally and vertically offering unlimited storage space. When ganging cabinets: rough opening width/height = total width/height of all cabinets and lights minus 3/4” (1.9 cm).

Stack filler is required for vertical stacking.

Recessed cabinets project 7/8” (2.2 cm) from wall.



Electrical Connection Detail (Rear View)



Product Diagram