


Features

- Dimmable LED LUM[™] task lighting with integrated touch control
- 4100K LED Color Temperature
- 55 footcandles of task lighting
- CRI90
- AiO cabinet can be paired with all M Series mirrored and decorative glass side kits
- Quiet close Safeseal[®] Gasket
- Mirrored interior with 6 adjustable glass shelves
- Includes magnetic tool holder
- Includes Compact Adjustable Magnifying Mirror (CAMM)
- Includes installation hardware for recess mounting
- Can be recessed or surface mounted (surface mounting kit required)
- Includes two USB charging ports and two 120VAC outlet receptacles
- Interior Light
- Accessory track (Accessory Trays sold separately)



Construction

- Satin anodized aluminum body and door frame
- 3 mirror design – rear of cabinet and both sides of door
- Concealed finger pull-door edge
- Blum 170° self-closing hinges
- Safeseal[®] Gasket with sealed corners on cabinet body
- Adjustable shelving at 2" (51 mm) increments
- Single field wire into electrical shelf - Front access serviceability
- Interior Illumination

Codes/Standards Applicable

- Electric Option Models are ETL certified to:
UL 962
CSA Standard C22.2 No. 68

Dimensions

Height: 30" (762 mm)
Width: 35-1/4" (895 mm)
Depth: 4-5/8" (117 mm) Surface Mounted
7/8" (22 mm) Recessed

Options

- OM[™] Audio

Installation Options

Recessed Mount - Rough Opening – 29-1/4" H x 34-1/2" W x 4" D
(743 mm H x 876 mm W x 102 mm D)

Surface Mount - Reference Surface Mount Kit when ordering
MSMK30D4P – Mirror Kit
MSMK30D4## – Decorative Glass Kit*

*See Robern Price Book for a list of available finish options

Model Number Key

AiO Series	Cabinet	Width	Height	Depth	Door Style	Hinge Side	Options
A	C	36	30	D4	P2 = Double	L = Left	Blank = Without Robern Audio A = Robern Audio

Electrical System



- 120 VAC 60HZ 20A
- Field wire location as shown in drawing
- 1/2" conduit (Ø 7/8" actual) electrical knockout location shown below
- Included field wire cable clamp

Optional Accessories


- Assorted glass bins:
 - Small (GLASSBIN3.25)
 - Medium (GLASSBIN5.25)
 - Large (GLASSBIN8.5)
- Entice™ Magnifying Mirror with dock - ENTICEDOCK
- Entice™ Magnifying Mirror without dock - ENTICE
- Handle Kits - MHANDLEKIT

Robern Audio


- Vibrating Glass Technology - Resulting in a virtually hidden system
- Wide Dispersion - Almost 160 degrees from the door surface
- Bluetooth® Connection
- Range: Up To 30 feet / 9.1 meters (depending on interference)
- 2 Channel Stereo
- 20 Watts / Channel
- Supports most Android and iOS devices: Smartphones, PCs, Tablets, and other Bluetooth® enabled devices. Volume controlled by device.
- Audio amplifier with Bluetooth connectivity for wireless streaming of audio input
- Plays your music or audio preferences and selections from any Bluetooth enabled device.



Cabinet Dimensions



Rough-in Dimensions



Back of Cabinet - Wire Access Location