



**Features**

- Dimmable LED LUM™ task lighting with integrated touch control
- Includes two USB charging outlets (bottom and right side)
- Energy efficient LED lighting
  - 4100K CCT (Correlated Color Temperature)
  - 55 foot-candle at 18"
  - CRI 90+
  - 114 watt consumption
  - Equivalent to 540 watt incandescent

**Construction**


- Powder coated steel back frame
- Quality polished edge mirror
- Single field wire installation
- Constructed for surface mounting
- Includes installation hardware

**Codes/Standards Applicable**

- AiO Mirror is ETL certified to:
  - UL 1598
  - CSA Standard C22.2 No. 250.0

**Dimensions**

Height: 69-7/8" (1775 mm)  
 Width: 29-1/8" (740 mm)  
 Depth: 1-1/2" (38 mm)



**Model Number Key**

AiO	Mirror	Width	Height	Touch Switch Side	Mirror Style	Options
A	M	30	70	R = Right	FP = Flat	Blank = Without Robern Audio

## Electrical System

- 120 Vac 60Hz 1.2A - Field Wire location as shown in drawing  
1/2" conduit (7/8" actual) electrical knockout location shown  
(alternative location provided)

