

VM36H2D21P Cartesian_™ - Specification Sheet

Features

- Modular Vanity Build arrays both stacked and ganged
- Mates to both H1D21 (7.5" high) & H2D21 (15" high) Series
- Handleless ergonomic continuous drawer
- Plumbing drawer to allow clearance for drain
- Includes:
 - 1 glass center bin
 - 2 fully adjustable glass drawer dividers

Construction

- All aluminum and glass construction designed for disassembly and recycle, aluminum structural frame and drawer sides, glass drawer fronts, and safety backed glass drawer bottom
- Heavy duty, full extension, soft close drawers slides
- Constructed for wall hanging loads with stone tops
- Glass fronts and optional side kits are replaceable
- Includes installation hardware using secure structural bolts
- Glass side kits sold separately

Codes / Standards Applicable

- · Night Light Option is ETL certified to:
 - UL 2108
 - CSA Standard C22.2 No. 12
- Electric outlet accessory is ETL certified to:
 - UL 1363
 - CSA Standard C22.2 No. 21

Dimensions


Height: 15" (381 mm)


Width: 36-1/8" (918 mm) - with side kits installed

Depth:21-3/4" (552 mm)


Configurable Options

- Choice of split plumbing or full width drawer
- Integrated LED night light Light bar built into top frame provides drawer illumination
- Glass finish options: Mirror, patterned glass, and back painted glass - gloss or matte
- Other widths available 12" (308 mm) / 24" (613 mm) / 30" (765 mm)
- 7-1/2" (191 mm) drawer height available H1
- Shallow depth available 18-3/4" (476 mm) D18
- In-drawer electrical outlets





Two H2 - 15" (381 mm) Cartesian vanities stacked Total height 30" (762 mm)



(2) H2 Cartesian vanities stacked (4) H1 Cartesian vanities stacked vanities stacked vanities stacked

Model	Number K	ey
-------	----------	----


	Width	Height	Depth	Drawer Style	Glass Finish		Night light Option
VM	36	H2	D21	P = Plumbing	11 = Tinted Grey Mirror	22 = Beach	N = Base Unit (Not Included)
					16 = Matte Sand	26 = Matte White	L = 5000K
				17 = Matte Slate	27 = Matte Gray	S = Selectable 2700K / 4000K	
					20 = Black 21 = White	28 = Matte Black 60 = Reeded White	
					21 - White	61 = Reeded Writte	
						or - Needed Drass	
						12 = Satin Bronze	
						19 = Satin White	

Electrical System

- Night light option 12VDC plug-in transformer Locate wall outlet as per installation instructions 209-1232
- In-drawer 3 outlet and switch box option plug-in cord Locate wall outlet as per installation instructions 209-1232 120VAC 20A outlet - GFCI protected

Add-On Accessories

- Insert Plumbing Drawer (VADRAWER36P)
- In drawer electrical outlets (VAELECTRIC21)
- Assorted glass bins:
 - Divided storage (GLASSBIN6.38)
 - Medium (GLASSBIN5.25)
- Small (GLASSBIN3.25) • Large (GLASSBIN8.5)
- Hair Styling Organizer (VAHAIRORG)
- Robern Engineered Stone Tops and porcelain sink available




Top view for plumbing and sink clearance

Modular Kits


Available in 4 heights (based on final configuration)

- Side kits (Single):
 - 7-1/2" (VM1SKH1D21##)
 - 22-1/2" (VM1SKH3D21##)
- Side kits (Pair):
 - 7-1/2" (VM2SKH1D21##)
 - 22-1/2" (VM2SKH3D21##)
- Ganging kits:
 - 7-1/2" (VMGKITH1)
 - •22-1/2" (VMGKITH3)
- Alcove finishing kits:
 - 7-1/2" (VMAKITH1) • 22-1/2" (VMAKITH3)

- 15" (VM2SKH2D21##)
- 30" (VM2SKH4D21##)
- 15" (VMGKITH2)
- 30" (VMGKITH4)
- 15" (VMAKITH2)
- 30" (VMAKITH4)



Side views for plumbing and sink clearance with door front



Front view with side kits

Installation Notes

Install this product according to the installation guide 209-1232.

- The Robern Engineered Stone Tops and porcelain sinks are recommended for this vanity.
- · Special site preparation is required. Wall bracing and Robern supplied hardware are recommended.
- If a sink will be installed, the plumbing must be roughed into the plumbing cutout area of the vanity. Refer to the sink rough-in and the vanity rough-in for proper placement. The water supply and drain lines must be installed before installing the vanity.

