



\*\*订购时请说明颜色编号  
\*\*Color code must be specified when ordering

11690T-7 入墙式切换阀体组件 11691T-7 入墙式阀体组件	11690T-7 入墙式切换阀体组件 11691T-7 入墙式阀体组件
<b>安装之前</b>	<b>BEFORE YOU BEGIN</b>
<p>所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。</p> <p>说明书包括重要的安装、保养及清洁方面的内容，请把这些资料交给用户阅读。</p> <p><b>注意事项：</b></p> <ol style="list-style-type: none"><li>1. 切断供水管路。</li><li>2. 遵守所有当地管路安装及建筑条例。</li><li>3. 在提示之前不要取下保护套。</li><li>4. 切换器正常工作最小压力为0.05MPa(0.5bar)。</li><li>5. 螺母锁紧扭矩65Nm~100Nm。埋墙前测试安装连接部位是否有渗漏，根据需要修理之。</li><li>6. 混合栓进水螺纹为Rc1/2"。</li><li>7. 本产品只接受水压测试，且测试前需先排空管路龙头之间的空气。测试水压不超过0.8MPa(8bar)，时间不超过30分钟。</li></ol>	<p>All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.</p> <p>Please leave these instructions for the consumer. They contain important information.</p> <p><b>NOTE:</b></p> <ol style="list-style-type: none"><li>1. Shut off the water supplies to the fitting.</li><li>2. Observe all local plumbing and building codes.</li><li>3. Do not remove the guards until instructed to do so.</li><li>4. The minimum inlet water pressure for the diverter is 0.05MPa(0.5bar).</li><li>5. Tighten the nuts to 65Nm~100Nm. Check for leaks before covering the pipes, repairs as needed.</li><li>6. Inlet threads of yoke are Rc1/2".</li><li>7. Please ensure only apply water pressure test on the product, and empty the air in pipe and faucet thoroughly before the test. Please ensure test pressure below 0.8MPa (8 bar) and test duration within 30 minutes.</li></ol>
<b>使用说明</b>	<b>HANDLE OPERATION</b>
顺时针旋转左把手打开热水，逆时针旋转右把手打开冷水。	Turn on the left handle clockwise is for hot water, turn on the right handle counter-clockwise is for cold water.
<b>安装尺寸</b>	<b>ROUGH-IN DIMENSIONS</b>

