




Recessed Dual-Handle Lavatory Faucet

14602T-4 入墙式双把脸盆龙头



^{**}订购时请说明颜色编号



INSTALLATION INSTRUCTIONS

萝瑞 *ZOURE*

安装说明书

Recessed Dual-Handle Lavatory Faucet

14602T-4 入墙式双把脸盆龙头

安装之前

所有的资料是按最新出版的产品资料编写而成。科 勒公司保留任何时候不经通知即可改变产品特性、 包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容, 请把这些资料交给用户阅读。

注意事项:

- 1.一定要先彻底冲洗供水管以清除管道中的杂质。
- **2**. 检查供水管有无损坏和漏水。如需要,进行替换和维修。
- 3.遵守当地管路安装条例。
- 4. 埋墙前测试安装连接部位是否有渗漏,根据需要修理之。
- 5.水龙头的最高工作压力: 0.4 MPa(4 bar), 当水压超过0.4 MPa(4 bar)时必须安装减压阀。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

NOTES:

- 1. Flush the water supply pipes thoroughly to remove debris
- 2. Inspect the supply tubing for damage and leakage. Replace and maintain as necessary.
- Observe local plumbing codes.
- 4. Check for leaks before cover the pipes, repairs as needed.
- 5. The highest working pressure for faucet is 0.4 MPa (4 bar). If it exceeds 0.4 MPa (4 bar), a pressure reducer is needed, or it maybe damage the faucet.

使用说明


逆时针旋转左把手打开热水,顺时针旋转右把手打 开冷水。

OPERATION INSTRUCTIONS

Turn on the left handle counter-clockwise is for hot water, turn on the right handle clockwise is for cold water.

安装尺寸

ROUGH-IN DIMENSIONS



1114585-2-B **4** 1114585-2-B


^{**}Color code must be specified when ordering

安装步骤

如何安装混合栓

切勿在此时将保护套(1)移去。

连接螺纹为G1/2"的供水管(2)至混合栓进水处(3)。供水管路中心线与装修好的墙面之距离应为72mm至84mm。贴红点3一侧朝左,安装热水管。



INSTALLATION

How To Install The Yoke


Do not take off guards (1) at this moment.

Connect the G1/2" water supply pipes(2) to the supply yoke(3). Keep the distance from centerline of the water supplies to the surface of the finished must be between 72mm and 84mm. Make sure the left supply pipe is the hot supply and connected to the end with red mark.


如何安装把手

墙壁装修好以后,可将阀体的保护套扔掉。

将橡胶垫片(6)装到装饰盖底座(7)背部凹槽,用工具(5)将装饰盖底座旋到阀体(3)上并贴紧墙壁。



阀处于关闭位置把手的状态如图所示。



How To Install The Handles

Remove and discard the guards after completed the finished wall.

Put the rubber washers(6) into the rear groove of the escutcheon bases(7). Screw the escutcheon bases onto the yoke(3) until against the finished wall with the key(5).


Keep screw holes facing downwards, place the handle kits(8) onto the escutcheon bases with the valves closed. (**Notes:** The handle kit with red mark should be installed on the left side). Secure handle kits by tightening the screws(9) with 2mm hex wrench(4).


The illustration shown is the correct position of the handles in the off position.

如何安装出水口

墙壁装修好以后,可将出水口的保护套 扔掉。

将不干胶垫片(13)粘到装饰盖底座(14)背部,检查O型圈(15)是否如图示装入装饰盖底座内槽中。将装饰盖底座装到出水口接头(12)上并贴紧墙壁。将螺钉(16)穿过装饰盖底座旋到固定环(11)上。锁紧。安装出水口组件(10),用2mm六_角扳手(4)将螺钉(9)锁紧。





How To Install The Spout

Remove and discard the guards after completed the finished wall.

Stick the adhesive washer(13) onto the rear of the escutcheon base(14). Check if the O-rings(15) are in the grooves of escutcheon base as figure shown. Put escutcheon base onto the spout adapter(12) until against the finished wall. Tighten the screws(16) onto thread ring(11) through escutcheon base. Install the spout kit(10). Tighten the screw(9) with 2mm hex wrench(4).


Notes: The spout kit bottom with flow restrictor, it can't be taken out, it must be clear regularly.

如何安装排水器

把锁紧螺母(21)、塑料垫片(20)、橡胶垫圈(19)从排水器本体上取下。把排水本体从脸盆上部孔插入。再依次将橡胶垫圈(小面朝上)、塑料垫片和锁紧螺母从排水本体底部装入。锁紧螺母。

注意: 如果需要,可以直接在排水器盘片(17)底面沿周围涂上一圈密封油灰,而不使用垫片(18)。

在锁紧螺母转紧后,不可调整排水本体的位置,否则会破坏油灰密封或密封剂 密封。去除多余的油灰。



How To Install The Drain

Remove the locknut(21), plastic washer(20), rubber gasket(19) from the drain body. Insert the drain body into the lavatory. Put the rubber gasket (Tapered side up), plastic washer and locknut back to the drain body in turn. Tighten the locknut.

Notes: If needed, apply a ring of plumbers putty around the underside of the drain flange(17) instead of using the washer(18).

Do not reposition the drain after the locknut is tightened, or you may break the putty or sealant seal. Remove any excess putty.

安装结果检查

确保已拧紧所有连接处。确保把手在 关闭的位置。

打开排水器和主要供水源,检查并修理有漏水的接口。

用1.5mm六角扳手(23)旋松螺钉(24),用工具(22)下心地卸下起泡器(25)。打开水龙头,让水流过出水口一分钟以清除杂质。冲洗起泡器,关闭龙头,保持固定孔朝下重新装回起泡器。

Fixing Hole 固定孔 24 23 25 22

INSTALLATION CHECKOUT

Ensure that all connections are tight. Ensure that the handles are in the off position.

Turn on the drain and main water supply, and check for leaks. Repair as needed.

Loosen screw(24) with 1.5mm hex wrench(23). Remove the aerator(25) carefully with key(22). Turn on the faucet. Run the water through the spout for about one minute to remove any debris. Remove any debris from the aerator. Shut off the faucet. Keep the fixing hole facing downwards, reinstall the aerator.

更换止水垫及活塞组件

逆时针旋下止水塞(26),然后取出止水垫(27)。更换新的止水垫。逆时针旋下活塞组件(28),更换新的活塞组件。装回止水垫及止水塞。



Replacing the Washer and Piston Kit

Turn counter-clockwise to remove the stopper(26). Take out washer(27). Replace with a new one. Turn counter clockwise to remove the piston kit(28). Replace with a new one. Reinstall stopper and washer.

清洗说明

适用于所有加工处理过的表面:以中性肥皂水清洗镀层表面,再以干净的软布彻底擦干整个表面,有许多清洁剂,比如氨水、去污粉及洁厕灵等,会对电镀表面造成伤害,切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

1114585-2-B **2** 1114585-2-B