

### Features

- Vitreous china
- European bowl
- Includes quiet close seat
- Includes polished chrome push button dual flush
- Wash down flushing system
- Dual flush 3/6 lpf
- 305 mm rough-in for S-Trap  
or 185 mm rough-in for P-Trap
- 85 mm glazed trapway
- 95 mm x 110 mm water area
- 700 mm x 370 mm x 775 mm

### TWO-PIECE TOILET 3/6L K-18182MY



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2
- TIS 792
- MS 147
- MS 795
- SS 378
- SS 379

### Colors/Finishes

- 0: White

### Accessories:

- 0: White
- CP: Polished Chrome

### Specified Model

Model	Description	Color/Finished
K-18182MY	Panache 3/6L Toilet W/O Seat	0: White

Recommended Accessories		Color/Finished
K-8827X	Odeon Quiet Close Toilet Seat	0
1066987	S-Trapway Connector	-
1138552	P-Trap Connector Assy	-

### Product Specification:

The European two-piece toilet shall be made of vitreous china. The toilet shall be 370 mm in length, 700 mm in width, and 775 mm in height with a 95 mm x 110 mm water area. Toilet shall be 305 mm rough-in for S-trap or 185 mm rough-in for P-trap. Toilet shall have 85 mm glazed trapway and polished chrome push button dual flush. Toilet shall be 3/6 L with wash down flushing system.

# PANACHE

## Technical Information

Fixture:	
Configuration	2-piece, European
Water per flush	3/6 L
Passageway	85 mm
Water area	95 x 110 mm
Water depth from rim	245 mm
Seat post hole centers	155 mm




Included Components:	
Bowl	K-15248K-0
Tank	K-18153K-NL-0
Tank cover	1082443-0

Included Components:	
Floor mounting kit	1072240
Fill valve	1095296
Flush valve	1118237
Tank gasket	1032265
Tank accessory pack	1050618
Top push button kit	1142420-CP

## Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.  
Unit: mm.



## Product Diagram