

MIRRORED CABINET K-30495X-L

Features

- Anodized aluminum construction with a durable rust-free
- For surface-mount installation
- One door (Left open)
- Soft touch control to adjust brightness / color temperature (3000K / 4000K / 6500K)
- Sensor Activation
- Copper Free mirror
- Fog-free mirror
- Used electrical power supply 220V 50Hz
- Three adjustable glass shelves
- Adjustable hinges with 100 degree opening capability
- Built-in power outlet for easy use of hair dryers, electric shavers and other common electrical equipment
- 591 x 133 x 762 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI/KCMA A 161.1-2000
- QB/T2189-1995

Installation Notes

Install this product according to the installation guide.




Specified Model

Model	Description	Color/Finished
K-30495X-L	Grooming mirrored cabinet, 600 mm - left	NA: Not Applicable

Recommend Accessories		
K-30498X	Grooming mirrored cabinet, 300 mm	NA: Not Applicable

Dimensions are approximate.
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram



คุณลักษณะ

- โครงตู้กระจกผลิตจากอลูมิเนียม อนโนไดซ์ ทนทานต่อการเกิดสนิม
- ติดตั้งแบบแขวน
- แบบ 1 ประตู (เปิดซ้าย)
- ระบบสัมผัสเพื่อปรับระดับความสว่างและอุณหภูมิสี (3000K / 4000K / 6500K)
- ระบบเปิด-ปิดไฟอัตโนมัติ
- เนื้อกระจกปราศจากทองแดง
- กระจกชนิดไล่ฝ้า
- ใช้ไฟฟ้า 220 โวลต์, 50 เฮิร์ตซ์
- กระจกชั้นวาง 3 ชั้น แบบปรับระดับได้
- บานพับปรับระดับ, เปิดกว้าง 100 องศา
- ช่องเสียบไฟในตัวสำหรับไดร์เป่าผม, ที่โกนหนวดไฟฟ้า และอุปกรณ์อื่นๆ
- 591 x 133 x 762 มม.

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI/KCMA A 161.1-2000
- QB/T2189-1995

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-30495X-L	ตู้กระจก 600 มม. รุ่นกรูมมิ่ง	NA: สีตามชนิดวัสดุ

อุปกรณ์ที่แนะนำ		
K-30498X	ตู้กระจก 300 มม. รุ่นกรูมมิ่ง	NA: สีตามชนิดวัสดุ

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์