

MIRRORED CABINET K-30498X

Features

- Anodized aluminum construction with a durable rust-free
- For surface-mount installation
- One door
- Double-sided, Folding Mirror
- Three adjustable glass shelves
- Adjustable hinges with 100 degree opening capability
- 300 x 133 x 762 mm

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI/KCMA A 161.1-2000
- QB/T2189-1995

Installation Notes


Install this product according to the installation guide.



Specified Model

Model	Description	Color/Finished
K-30498X	Grooming mirrored cabinet, 300 mm	NA: Not Applicable

Dimensions are approximate.
Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- โครงตู้กระจกผลิตจากอลูมิเนียม อนโนไดซ์ ทนทานต่อการเกิดสนิม
- ติดตั้งแบบแขวน
- แบบ 1 ประตู
- กระจกเปิดสองชั้น แบบพับได้
- กระจกชั้นวาง 3 ชั้น แบบปรับระดับได้
- บานพับปรับระดับ, เปิดกว้าง 100 องศา
- 300 x 133 x 762 มม.

มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI/KCMA A 161.1-2000
- QB/T2189-1995

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-30498X	ตู้กระจก 300 มม. รุ่นกรูมมิ่ง	NA: สีตามชนิดวัสดุ

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์