

EXPOSED WALL-MOUNT SHOWER MIXER K-24749X-4

Features

- Brass construction
- G1/2" thread connection
- Durable Kohler finishes resist corrosion and tarnishing
- Leak-free ceramic disc valve with lifetime warranty
- Adjustable inlet fittings with 15 mm tolerance
- Includes Renew, 3 function handshower
- Includes 1.5 m shower hose, chrome color
- Includes adjustable bracket

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552

Installation Notes


Install this product according to the installation guide.



Specified Model

Model	Description	Color/Finished
K-24749X-4	Honesty exposed wall-mount shower mixer	CP: Polished Chrome


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

ก๊อกผสมเย็นอาบแบบติดผนัง พร้อมฝักบัวสายอ่อน **K-24749X-4**



คุณลักษณะ

- ผลิตจากทองเหลือง
- เกลียวข้อต่อขนาด G1/2"
- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- เซรามิกวาล์วป้องกันการรั่วซึม รับประกันตลอดอายุการใช้งาน
- อุปกรณ์ติดตั้งกับท่อน้ำเข้าปรับระยะได้ 15 มม.
- พร้อมฝักบัวสายอ่อนรุ่น รีโนว ปรับสายน้ำได้ 3 ระดับ
- พร้อมสายฝักบัวสีโครมยาว 1.5 เมตร
- พร้อมขอแขวนฝักบัวปรับระดับ

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-24749X-4	ก๊อกผสมเย็นอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นอเนสตี	สี/วัสดุเคลือบผิว
	ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน	CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์