


Bath/Shower Faucet

12778T 72629T 挂墙式浴缸花洒龙头 12779T 72630T 挂墙式花洒龙头



KOHLER® INSTALLATION INSTRUCTIONS

Bath/Shower Faucet

安装说明书

12778T 72629T 挂墙式浴缸花洒龙头 12779T 72630T 挂墙式花洒龙头

安装之前

所有的资料是按最新出版的产品资料编写而成。科 勒公司保留任何时候不经通知即可改变产品特性、 包装或产品可供类型的权利。

说明书包括重要的安装、保养及清洁方面的内容, 请把这些资料交给用户阅读。

注意事项:

- 1. 一定要先彻底冲洗供水管以清楚管道中的杂质。
- 2. 切换器正常工作的最小压力为0.05MPa(0.5bar)。
- 3. 花洒最高工作压力: 0.5MPa(5bar)。水压超过 0.5MPa(5bar)须安装减压阀。花洒最高工作温度及 环境温度: 60°C。请特别注意花洒同花洒连接的臂 管须远离浴霸, 否则可能损坏花洒及其密封件, 甚 至对使用者造成伤害。

BEFORE YOU BEGIN

All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.

Please leave these instructions for the consumer. They contain important information.

NOTES:

- 1. Flush the water supply pipes thoroughly to remove
- 2. The minimum inlet water pressure for the diverter is 0.05MPa(0.5bar).
- 3. The highest working pressure for handspray is 0.5MPa(5bar). If it exceeds 0.5MPa(5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handspray, showerhead and the shower arm away from heater, or it may become damaged and cause injury to the user.

使用说明


将手柄轻轻提起, 向上转为热水, 向下转为冷水。

HANDLE OPERATION

Lift the handle gently. Turn upwards for hot water, turn downwards for cold water.

安装尺寸

ROUGH-IN DIMENSIONS




1092292-2-A 1092292-2-A

安装说明

为使安装顺利, G1/2"内螺纹管道配件(客户自备)应已装好, 预留150mm的间距, 保持水平, 并深浅合适。

彻底冲洗供水管,以清除管路中的杂质。



Flush the water supply pipes thoroughly to remove debris.

Apply appropriate thread sealants or

thread tape on connectors. Install the

two offset connectors(1) into the hot

and cold supply pipes.

To perform installation, installer must

provided), spaced 150mm apart, level


and keep proper position in the wall.

provide G1/2" female supply fittings(not

INSTALLATION

在两个接头(1)涂上螺纹密封膏或缠绕密封胶带,然后旋入冷热供水管中。

调节两个接头,使其中心距离为 150mm并保持同一水平。它们凸出墙 面的尺寸应在40到45mm之间。将装饰 罩(2)套入接头,紧贴装修后的墙壁。




Adjust center-to-center distance between the connectors to 150mm and level. They should extend 40 to 45mm from finished wall. Thread escutcheons (2) onto the connectors until they contact the fininsed wall.

将垫片(3)放入螺母(4)中,把螺母旋到接头(1)上,用带状扳手锁紧。

Put the washers(3) into the nuts(4). Thread the nuts onto the connectors(1) and tighten by wrench.

注意: 对于12778T和72629T, 需要先去掉保护套。

垫片(6-1, 厚3mm)装入到软管(7)的A端, 然后与出水口(5)连接。将垫片(6-2, 厚5mm)装入软管的B端接到花洒(8)上。




NOTES:For 12778T & 72629T, remove the guard on the outlet connector firstly.

Put the washer(6-1, 3mm) into end A of the hose(7), and then connect to the faucet outlet(5). Put the washer(6-2, 5mm) into end B of the hose(7), and connect hose to the handspray(8).

如何安装托架

在墙面选一合适的位置来安装托架。

根据孔距在墙面标记位置,依据胀塞 (9)直径打孔,安装胀塞。旋紧螺钉 (10),使底座(11,平面朝上)固定紧贴 墙壁。将托架(12)扣在底座上,使凸台 嵌入豁口。把花洒挂在托架上。



How To Install The Bracket

Determine a suitable location on the finished wall to install the bracket.

Mark bracket base mounting hole locations on the wall according to the dimension. Drill two holes in the finished wall, the holes should match the anchors(9). Install the anchors. Tighten screws(10) to secure bracket base(11) to the fininsed wall. Put the bracket(12) onto the bracket base and lock by stopper. Hang the handspray on the shower bracket.

安装结果检查

检查并确保所有的衔接处都已拧紧。

确保手柄在"关"的位置。

打开排水系统和主要供水源,检查并 修理有漏水的接口。

浴缸花洒龙头:

取下花洒并用附带的工具(14)取下整流器(13)。打开冷热水,让水流出约一分钟以清除杂质。检查渗漏,清洗整流器。关闭水龙头,并装回整流器和花洒。

Ensure that all coupling nuts are tighten.

INSTALLATION CHECKOUT

Ensure that the handle is in the off position.

Turn on the main water supply, and check for leaks. Repair as needed.

Bath & Shower Faucet:

Remove the handspray. Remove the stream breaker(13) by key(14). Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Remove any debris from the stream breaker. Shut the faucet off. Reinstall the stream breaker and handspray.

Shower Faucet:

Remove the handspray. Run hot and cold water through the faucet for about one minute to remove any debris. Check for leaks. Shut the faucet off. Reinstall the handspray.

花洒龙头:

取下花洒。打开冷热水,让水流出约一分钟以清除杂质。检查渗漏。关闭水龙头,并装回花洒。

清理说明

适用于所有加工处理过的表面:以中性肥皂水清洗 镀层表面,再以干净的软布彻底擦干整个表面,许 多清洁剂,比如氨水、去污粉及洁厕灵等,会对电 镀表面造成伤害,切忌使用。

有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。

CLEANING INSTRUCTIONS

All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.

Do not use abrasive cleaners or solvents on Kohler faucets and fittings.

1092292-2-A **2** 1092292-2-A **3**