


	
<p>在软管(30)的连接螺母内放入垫片, 并将其锁紧到切换器(31)的花洒接口(带单向阀的的一端)上。在软管(32)的两端连接螺母内分别放入垫片, 连接T型接头(12)和切换器的进水接口。然后用长40cm的软管(33)连接两阀体(35), 最后用软管(34)连接浴缸出水口和切换器的另一端接口。锁紧所有的连接螺母。</p> <p>为保证水流顺畅, 花洒抽取自如, 应该避免软管打结、缠绕。</p> <p>注意: 切换器接口带单向阀的一端必须连接到花洒, 切勿接到出水口。软管只能用在指定部位。</p>	<p>Put the fiber washer into connecting nut of the hose(30), then thread the nut to the end with deck-valve of diverter(31). Put the fiber washer into each connecting nut of the hose(32), then connect the Tee(12) and inlet end of the diverter. Connect the side bodies(35) with the hose(33)(length 40cm). Connect the spout and the other end of the diverter with the hose(34). Tighten all the connecting nut.</p> <p>To ensure the water flow smoothly and the handspray can be drawn out easily, the hose should avoid kinking, twisting.</p> <p>Note: The end with the check valve of diverter must be connected to the handspray. Hoses should only be used where indicated.</p>
安装结果检查	INSTALLATION CHECKOUT
<p>确保已拧紧所有连接处。确保把手在“关”的位置。取下起泡器(36)及花洒(28)。打开主供水源, 检查泄漏。打开冷热水阀, 使水流过出水口, 除掉杂物, 关闭阀。重新安装起泡器。</p> 	<p>Ensure that all connections are tight. Ensure that the handles are in the off position. Remove the aerator(36) and handspray(28). Open the drain. Turn on the main supply and check for leaks. Open both hot and cold valves and run water through the spout to remove any debries. Turn the valve off. Reinstall the aerator and handspray.</p> <p>Gently rotate the handspray head. You can get three different flows signed on handspray head.</p>
清理说明	CLEANING INSTRUCTIONS
<p>适用于所有加工处理过的表面: 以中性肥皂水清洗镀层表面, 再以干净的软布彻底擦干整个表面, 许多清洁剂, 比如氨水、去污粉及洁厕灵等, 会对电镀表面造成伤害, 切忌使用。</p> <p>有磨损性的清洁用具或清洁剂也不可使用于科勒牌的水龙头及其配件上。</p>	<p>All Finishes: Clean the finish with mild soap and warm water. Wipe entire surface completely dry with clean soft cloth. Many cleaners may contain chemicals, such as ammonia, chlorine, toilet cleaner etc. which could adversely affect the finish and are not recommended for cleaning.</p> <p>Do not use abrasive cleaners or solvents on Kohler faucets and fittings.</p>

<div><div><div>KOHLER®</div><div>INSTALLATION INSTRUCTIONS</div><div>安装说明书</div></div><div><div>艾丽维</div><div>ELEVATION</div><div>Deck-Mount Faucet With Handspray</div></div></div>	
18876T 72681T 缸边(台面)式浴缸花洒龙头	
安装之前	BEFORE YOU BEGIN
<p>所有的资料是按最新出版的产品资料编写而成。科勒公司保留任何时候不经通知即可改变产品特性、包装或产品可供类型的权利。</p> <p>说明书包括重要的安装、保养及清洁方面的内容, 请把这些资料交给用户阅读。</p> <p>注意事项:</p> <ol style="list-style-type: none">一定要先彻底冲洗供水管以清除管道中的杂质。切断供水管路。检查供水管有无损坏。如需要, 进行替换。遵守当地管路安装条例。尽可能在安装浴缸之前安装水龙头。花洒最高工作压力: 0.5MPa(5bar)。水压超过0.5MPa(5bar)须安装减压阀。花洒最高工作温度及环境温度: 60°C。请特别注意花洒同花洒连接的臂管须远离浴霸, 否则可能损坏花洒及其密封件, 甚至对使用者造成伤害。	<p>All information is based on the latest product information available at the time of publication. Kohler Co. reserves the right to make changes in product characteristics, packaging, or availability at any time without notice.</p> <p>Please leave these instructions for the consumer. They contain important information.</p> <p>NOTES:</p> <ol style="list-style-type: none">Flush the water supply pipes thoroughly to remove debris.Shut off the water supplies to the fitting.Inspect the supply tubing for damage. Replace as necessary.Observe local plumbing codes.If possible, install this faucet before installing the tub.The highest working pressure for handspray & shower head is 0.5MPa(5bar). If it exceeds 0.5MPa (5bar), a pressure reducer is needed. The highest water and environment temperature is 60°C. Please keep handspray, shower head and the shower arm away from heater, or it may become damaged and cause injury to the user.
安装尺寸	ROUGH-IN DIMENSIONS
	

18876T 72681T 缸边(台面)式浴缸花洒龙头



**订购时请说明颜色编号

**Color code must be specified when ordering