

### Features

- ToF sensing technology, able to work with special material lavatories like glass and stainless steel
- Strong anti-interference ability
- Durable KOHLER finishes resist corrosion and tarnishing
- 1000 mm flexible supply hose for easy installation
- Automatically stop when used continuous more than 1 minute
- 133 mm spout reach
- This product meets LEED water conservation requirements (K-72866X-BE2)

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB18145-2003
- C/J/T 194-2004

### Installation Notes

Install this product according to the installation guide.

### Technical Information

Sensor Duration	Less than 0.5s
Shut-off Delay	0.5~1s
Sensind Distance	Automatic adjustment
Flow Rate (K-72866X-B)	About 1.5 L/min
Flow Rate (K-72866X-BE2)	About 1 L/min
Ambient Temperature	1~55°C
Supply Water Temperature	0.5~71°C
Supply Water Pressure	0.05~0.86 MPa

### Specified Model


Model	Description	Color/Finished
K-72866X-B	Strayt cold only toughless lavatory faucet	CP: Polished Chrome
K-72866X-BE2	Strayt cold only toughless lavatory faucet	CP: Polished Chrome

### Required Accessories

K-16305X	AC power unit	N/A: Not Applicable
----------	---------------	---------------------


Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

## COLD ONLY TOUCHLESS LAVATORY FAUCET K-72866X-B ALSO K-72866X-BE2



Flow Curve

Note: Flow rates are approximate.

(1 gallon = 3.785 liters, 1 bar = 14.5 psi)

### Product Diagram

