

#### Features

- Brass construction
- Precise thermostatic valve with over-ridable temperature stop for added safety
- Durable KOHLER finishes resist corrosion and tarnishing
- 200mm spout reach
- Adjustable inlet fittings with 15mm tolerance
- Includes 110 mm Awaken Geometric 3-function handshower

# **Codes/Standards Applicable**

Specified model meets or exceeds the following:

- EN 1111-1998
- QB 2806-2006
- GB 18145-2014


### **Installation Notes**

Install this product according to the installation guide.

## **Specified Model**


Model	Description	Color/Finished
72286T-9	Aleo Exposed Wall Mount Thermostatic Bath Shower Faucet	Polished Chrome (CP)
72352T-9	Aleo Exposed Wall Mount Thermostatic Shower Only Faucet	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.



Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi) 2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate. Unit: mm



## **Product Diagram**

EXPOSED WALL MOUNT THERMOSTATIC FAUCET



ALEO

