

Features

- Premium metal construction
- · Leak-free ceramic disc valve with lifetime warranty
- Durable KOHLER finishes resist corrosion and tarnishing
- Flexible G1/2" supply hoses
- Lever handle(s)
- 123mm spout reach
- Robust, easy-access mounting hardware ensures secure installation and hassle-free maintenance
- Includes pop-up drain

Codes/Standards Applicable

Specified model meets or exceeds the following:

- GB 18145-2014
- EN 817-2008

Installation Notes

Install this product according to the installation guide.

SINGLE CONTROL LAVATORY FAUCET 72782T-4


ELLISTON



Specified Model

Model	Description	Color/Finished	
72782T-4	Elliston Single Control Lavatory Faucet	Polished Chrome (CP)	Brushed Nickel (BN)


For a full range of color finishes in your market please contact your local Kohler representative.



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. Unit: mm

The finished wall



Product Diagram