

### Features


- Vitreous china
- Elongated bowl
- Includes quiet close seat
- Includes polished chrome push button
- Siphonic Wash Down flushing system
- 3/4.8 liter per flush
- 305 mm rough-in for S-trap
- 734 x 391 x 776 mm

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.2/CSA B45.1
- CNS 3220

## TWO-PIECE TOILET WITH SEAT K-22241TW



### Technical Information

Fixture:	
Configuration	two-piece, elongated
Water per flush	3/4.8 liter
Passageway	51 mm
Water area	127 x 104 mm
Water depth from rim	240 mm
Seat post hole centers	140 mm

Included Components:	
Bowl	K-22242K-**
Tank	K-22243TW-**
Tank cover	1203722-SP-**
Quiet close seat	K-4087X-**

### Installation Notes


Install this product according to the installation guide.

### Specified Model

Model	Description	Color/Finishes
K-22241TW-S	Reach Concealed two-piece toilet, S-trap with quiet close seat	0: White

Dimensions are approximate. (Do not direct measure a dimensional from picture below.)

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

### Product Diagram