

### DUAL SHOWER COLUMN 72679T-C7

#### Features

- Brass construction
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage
- Leak-free ceramic disc valve with lifetime warranty
- Durable KOHLER finishes resist corrosion and tarnishing
- 134mm spout reach
- Adjustable inlet fittings with 15mm tolerance
- Hose connection for flexible installation
- Includes 10" ultra thin round Katalyst Air Rainhead
- Includes 110 mm Renew Organic 3-function handshower

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- EN 200-2008
- GB/T 23447-2009




#### Installation Notes

Install this product according to the installation guide.

#### Specified Model


Model	Description	Color/Finished
72679T-C7	ELEVATION Dual Shower Column-Angular	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.



- Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)  
2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.  
Unit: mm



#### Product Diagram