

Features

- Brass construction
- Optimized sprayface and large nozzles with Katalyst® Air-induction for improved water coverage
- Precise thermostatic valve with over-ridable temperature stop for added safety
- Durable KOHLER finishes resist corrosion and tarnishing
- 176mm spout reach
- Adjustable inlet fittings with 15mm tolerance
- Concentric volume and temperature control for simple and intuitive use
- Includes 10" ultra thin round Katalyst Air Rainhead
- Includes 120mm Rain Duet contemporary, 3-function handshower
- Includes mirror and soap dish kit

THERMOSTATIC DUAL SHOWER COLUMN WITH ACCESSORIES-DIRECT CONNECTION

99437T-C



Codes/Standards Applicable

Specified model meets or exceeds the following:

- EN 1111-1998
- QB 2806-2006
- GB/T 23447-2009




Installation Notes

Install this product according to the installation guide.

Specified Model


Model	Description	Color/Finished
99437T-C	URBANITY Thermostatic Dual Shower Column With Accessories-Angular	Polished Chrome (CP)

For a full range of color finishes in your market please contact your local Kohler representative.



- Note: 1. Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)
 2. Flow rates shown with supplied flow regulators installed.

Dimensions are approximate.
 Unit: mm



Product Diagram