

Features

- Durable KOHLER finishes resist corrosion and tarnishing.
- G 1/2" thread connection(s)
- 3-function hand shower.
- Include Rain function.
- Include Deep massage function.
- Include Cloud function.

HANDSHOWER K-28694T, K-R28694T K-28695T, K-R28695T



Codes/Standards Applicable

- Specified model meets or exceeds the following:
- TIS 2066-2552
 - GB/T 23447-2009

Installation Notes




Install this product according to the installation guide.

Specified Model




Model	Description	Color/Finishes	
K-28694T	Statement round hand shower w/watermind		<input type="checkbox"/> Other
K-R28694T	Statement round hand shower w/watermind	<input type="checkbox"/> CP: Polished Chrome	
K-28695T	Statement oblong hand shower w/watermind		<input type="checkbox"/> Other
K-R28695T	Statement oblong hand shower w/watermind	<input type="checkbox"/> CP: Polished Chrome	

Note: For a full range of color finishes in your market please contact your local Kohler representative.

K-28694T, K-R28694T




K-28695T, K-R28695T




Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate. (Do not direct measure a dimensional from picture below)
Unit: mm

K-28694T, K-R28694T



K-28695T, K-R28695T



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

Product Diagram

คุณลักษณะ

- วัสดุเคลือบผิวพิเศษจากโคห์เลอร์ คงทน เงางาม
- เกลียหัวฝักบัวขนาด G 1/2"
- หัวฝักบัวปรับสายน้ำได้ 3 รูปแบบ
- ฟังก์ชันนวดด้วยสายน้ำแบบสายฝน (Rain)
- ฟังก์ชันนวดด้วยสายน้ำแบบเกลียวผสม (Deep massage)
- ฟังก์ชันน้ำพ่นแบบละอองใหม่ นุ่ม เบา สบาย เหมาะสำหรับผิวหน้า (Cloud)

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552
- GB/T 23447-2009

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

หัวฝักบัวสายอ่อน K-28694T, K-R28694T K-28695T, K-R28695T






รุ่นผลิตภัณฑ์




รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-28694T	หัวฝักบัวกลมพร้อมวอเตอร์เมต รุ่นสเททเมนท์	<input type="checkbox"/> อื่นๆ
K-R28694T	หัวฝักบัวกลมพร้อมวอเตอร์เมต รุ่นสเททเมนท์	<input type="checkbox"/> CP: สีโครมเงา
K-28695T	หัวฝักบัวทรงรีพร้อมวอเตอร์เมต รุ่นสเททเมนท์	<input type="checkbox"/> อื่นๆ
K-R28695T	หัวฝักบัวทรงรีพร้อมวอเตอร์เมต รุ่นสเททเมนท์	<input type="checkbox"/> CP: สีโครมเงา

ตรวจสอบ สี/วัสดุเคลือบผิวผลิตภัณฑ์จากตัวแทนจำหน่ายโคห์เลอร์ในประเทศของท่าน

K-28694T, K-R28694T




K-28695T, K-R28695T




หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ (ห้ามวัดขนาดโดยตรงจากภาพด้านล่าง)
หน่วย: มม.

K-28694T, K-R28694T



K-28695T, K-R28695T



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

ภาพแสดงผลิตภัณฑ์