

### Features

- Vitreous china.
- Under-mount.
- Oval basin.
- No faucet holes; requires wall- or counter-mount faucet.
- Coordinates with other products in the Devonshire collection.
- 16-7/8" (430 mm) x 13-11/16" (348 mm)

### **Recommended Accessories**

K-9018 P-Trap

### Components

Additional included component/s: 1193643 Basin Clamps.



ADA

**Codes/Standards** 

ASME A112.19.2/CSA B45.1 ADA ICC/ANSI A117.1

# **KOHLER® One-Year Limited Warranty**

See website for detailed warranty information.

# **Available Color/Finishes**

Color tiles intended for reference only.




7 Black Black™



# **Devonshire**®

Under-mount Bathroom Sink K-2350



# **Technical Information**

**KOHLER** 

All product dimensions are nominal.	
Bowl configuration:	Single
Installation:	Under-mount
Bowl area (Only):	Length: 16-7/8" (429 mm)
	Width: 13-11/16" (348 mm)
	Water depth: 4-3/16" (106 mm)
Drain hole:	1-3/4" (44 mm)
Template:	1289470-7, required, not included

#### Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the current product template available at www.kohler.com, or by calling 1-800-4KOHLER. Kohler Co. is not responsible for cutout errors when the incorrect cutout template is used.

ADA compliant when installed to the specific requirements of these regulations.

