

Brochure
(English version)

Since 1873



Asia-Pacific: Kohlerasiapacific.com | Australia: Kohler.com.au | China: Kohler.com.cn | Hong Kong: Kohler.com.hk
Indonesia: Kohler.co.id | Korea: Kohler.co.kr | Malaysia: Kohler.my | New Zealand: Kohler.co.nz | Singapore: Kohler.com.sg
Taiwan: Kohler.com.tw | Thailand: Kohlerthai.com | The Philippines: Kohler.ph | Vietnam: Kohlernv.com | USA: Kohler.com
©2014 by Kohler Co.



Veil | When technology meets art

KOHLER®


Veil. When technology meets art

Balanced curves and ultra-responsive controls set the Veil toilet apart. The epitome of minimalist and ergonomic design, its sculpted form pairs with a suite of customized features fine-tuned to offer optimum hygiene and the ultimate in individual comfort. Veil, the perfect marriage of technology and art.





With its clean, refined lines, Veil is the height of contemporary design and function. Every detail is meticulously attended to, from the concealed tank and integrated mounting hardware to the self-sanitizing bidet. The result is a smart, easy-to-clean toilet with a sleek, seamless look.



French Curve Seat

The integrated French Curve Seat is ergonomically designed to minimize pressure points and enhance comfort. Additionally, the seat is made with antibacterial material for improved hygiene.



Remote Control

Designed to fit easily in your hand for one-touch control, the remote control offers ready access to the full menu of cleansing features.

Flushing System



Rimless bowl offers a cleaner flush with its 360 degree, all-around system.



Dual jets create a strong siphon for an efficient flush.



Powerful water flow eliminates bowl residue.

Sensor Activated

Adjustable sensor automatically opens and closes the seat cover. Choose from 3 available distance settings.



Multi-Function Dual Nozzles



Front wash: air-infused gentle cleansing with 78 fine nozzles



Rear wash: spiral spray offers broad cleansing coverage



Pulsating wash: intermittent spray cleanses and soothes



Oscillating wash: spray moves back and forth for more effective cleansing



UV-sanitizing: UV light disinfects wand automatically every 24 hours



Self-cleaning: wand is automatically washed with sterilized water after every use

Product Specifications

Flushing volume	3L/4.8L		
Minimum rough-in	305mm		
Minimum water supply pressure	0.1Mpa (dynamic pressure), up to 21L/min (flow)		
Maximum water supply pressure	0.74Mpa (static pressure)		
Specification	220V/220V-240V~, 50Hz/60Hz		
Rated power	960W (220V)/1000W (220V-240V)		
Maximum instantaneous power	1600W		
Power cord length	About 1.3m		
Outer dimension of product	670mm x 438mm x 533mm		
Product weight	About 46 Kg		
Operation environment	1-40°C		
Cleaning	Water flow (at 0.2 Mpa)	Rear	About 0.35-0.68L/min
		Spiral	About 0.26-0.68L/min
		Front	About 0.35-0.68L/min
	Cleaning water temp	Close, 1-5 levels (room temp, about 31-39 °C)	
	Cleaning time (Max)	300s	
	Quantity of nozzles	1 unit	
	Nozzle position adjustment	5 positions	
	Impulse massage	On/Off	
	Oscillating cleaning	On/Off	
	Safety devices	Overheating protection	Thermal fuse, overheating breaker
Backflow prevention		One-way valve	

Comfort	Heated seat	Heating power	About 40W	
		Temp adjustment	Close, 1-5 levels (room temp, about 31-39 °C)	
		Safety devices	Thermal fuse, overheating breaker	
	Cover	Automatic open/close, slow close, remote open/close		
	Seat	Slow close, remote open/close		
	Dryer	Air flow	About 0.22 m³/min	
		Heating power	About 200W	
		Temp adjustment	Close, 1-5 levels (room temp, about 31-39 °C)	
		Safety devices	Thermal fuse, overheating breaker	
	Deodorizer	Air flow	≥0.11 m³/min	
Hygiene	Self-cleaning nozzle		Yes	
	Anti-bacterial material		Seat and cover	
	Sterilized water		Yes	
	UV light		Yes	
Other	Auxiliary keyboard		6 function keys	
	Seating sensor		Capacitive sensing	
	Night light		Blue	
	Auto open/close cover		Microwave sensing	
	Manual flushing		Available under power failure condition	