


Features

- Kohler Cast iron sink
- Undercounter or self-rimming
- Double (equal) compartment
- Includes S-trap and P-trap, strainers, soap dispenser and wire basket
- 840 x 480 x 219 mm

KITCHEN SINK K-3885X-2SD ALSO K-3886X-2S



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-3885X-2SD	Indio cast iron kitchen sink	<input type="checkbox"/> 0
K-3886X-2S	Indio cast iron kitchen sink for Karbon faucet	<input type="checkbox"/> 0

Recommended Accessories		
K-668X	Candide kitchen faucet (K-3885X-2SD)	<input type="checkbox"/> CP
K-6227	Karbon kitchen faucet (K-3886X-2S)	<input type="checkbox"/> CP

Product Specification:

The undercounter kitchen sink shall be made of Kohler Cast iron sink. Sink shall be 840 mm in length and 480 mm in width and 219 mm in depth. Sink shall be double (equal) compartment. Sink shall include S-trap and P-trap, strainers, soap dispenser and wire basket. Sink shall be Kohler Model K-____-____-NA.

INDIO

Technical Information

Fixture*:		
Basin area	left	370 x 405 mm
	right	280 x 285 mm
Water depth	left	130 mm
	right	130 mm
Drain hole		38 mm
Faucet hole		34 mm
Handle hole (K-3886X-2S)		54 mm
*Approximate measurements for comparison only.		


Included components:	
S-trap	8851T-NA
P-trap	1199152
Strainer	8818T-NA
Soap dispenser	2983T-NA
Wire basket	1144112
Template	1150340-X7

Installation Notes


Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm.

K-3885X-2SD



K-3886X-2S




Product Diagram

คุณลักษณะ

- ผลิตจากเหล็กหล่อ (Kohler Cast iron)
- แบบฝังใต้เคาน์เตอร์หรือฝังบนเคาน์เตอร์
- สองหลุม
- พร้อมข้อต่อน้ำทิ้งแบบลงพื้นและแบบออกผนัง, สะดืออ่าง, ที่ใส่น้ำยาล้างจาน และตะแกรง
- 840 x 480 x 219 มม.

อ่างล้างจาน K-3885X-2SD ALSO K-3886X-2S



มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- ANSI A112.19.3M/CSA B45.4
- QB/T 4013

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-3885X-2SD	อ่างล้างจาน สองหลุม รุ่น อินดิโอ	<input type="checkbox"/> 0
K-3886X-2S	อ่างล้างจาน สองหลุม รุ่น อินดิโอ สำหรับติดตั้งคู่กับก๊อกน้ำรุ่น คาร์บอน	<input type="checkbox"/> 0

แนะนำใช้ร่วมกับผลิตภัณฑ์รุ่น

K-668X	ก๊อกอ่างล้างจาน รุ่น แคนดิด (K-3885X-2SD)	<input type="checkbox"/> CP
K-6227	ก๊อกอ่างล้างจาน รุ่นคาร์บอน (K-3886X-2S)	<input type="checkbox"/> CP

ข้อมูลผลิตภัณฑ์:

อ่างล้างจานแบบฝังใต้เคาน์เตอร์ซึ่งผลิตจากเหล็กหล่อ (Kohler Cast iron) อ่างล้างจานมีขนาดยาว 840 มม. กว้าง 480 มม. และสูง 219 มม. อ่างล้างจานเป็นชนิดสองหลุม อ่างล้างจานพร้อมข้อต่อน้ำทิ้งแบบลงพื้นและแบบออกผนัง, สะดืออ่าง, ที่ใส่น้ำยาล้างจาน และตะแกรง อ่างล้างจานรุ่นนี้คือ อ่างล้างจานโคห์เลอร์รุ่น K-____-____-NA

อินดิโอ

ข้อมูลเฉพาะ

ผลิตภัณฑ์*:		
พื้นที่อ่าง	ซ้าย	370 x 405 มม.
	ขวา	280 x 285 มม.
ระยะน้ำลึก	ซ้าย	130 มม.
	ขวา	130 มม.
ขนาดรูท่อน้ำทิ้ง		38 มม.
ขนาดรูก็อกน้ำ		34 มม.
ขนาดรูมือปิดก็อกน้ำ (K-3886X-2S)		54 มม.
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น		

ส่วนประกอบผลิตภัณฑ์:	
ข้อต่อน้ำทิ้งแบบลงพื้น	8851T-NA
ข้อต่อน้ำทิ้งแบบออกผนัง	1199152
สะดืออ่าง	8818T-NA
ที่ใส่น้ำยาล้างจาน	2983T-NA
ตะแกรา	1144112
กระดาษแม่แบบ	1150340-X7


ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยดูจากข้อแนะนำการติดตั้ง



ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.

K-3885X-2SD



K-3886X-2S



ภาพแสดงผลิตภัณฑ์

อ่างล้างจาน รุ่น อินดิโอ

หน้า 4/4

1150340-X4-B

KOHLER