


Features

- Acrylic and reinforced with fiberglass
- Drop-in
- Includes pillow head
- Includes pop-up drain and overflow
- Coordinates with Patio suite
- 1600 x 750 x 450 mm

BATH K-45699X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- TIS 2141-2546

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-45699X	Patio 1600 plain bath	0

Product Specification:

The Patio bath shall be 1600 mm in length, 750 mm in width, and 450 mm in height. Bath shall be made of acrylic and reinforced with fiberglass. Bath shall be drop-in installation. Bath shall be coordinating Patio suite. Bath shall include pillow head, pop-up drain and overflow. Bath shall be Kohler Model K-45699X-_____.

PATIO 1600


Technical Information

Fixture*:	
Basin area:	
Basin area bottom	955 x 365 mm
Basin area top	1400 x 670 mm
To overflow:	
Water depth	320 mm
Capacity	154 liter
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	21 kg
*Approximate measurements for comparison only.	

Installation Notes

Install this product according to the installation guide.
 Floor support under bath must provide for a minimum of 250 kg/square meter loading.

Dimensions are approximate.
 Unit: mm




Product Diagram

คุณลักษณะ

- อะครีลิกเสริมใยแก้ว
- แบบฝัง
- พร้อมหมอนรองศีรษะ
- พร้อมตะได้อ่างแบบป๊อปอัพและท่อน้ำล้น
- เหมาะสำหรับชุดแพททีโอ
- 1600 x 750 x 450 มม.

อ่างอาบน้ำ

K-45699X



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z124.1.2
- มอก. 2141-2546

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-45699X	อ่างอาบน้ำ รุ่น แพททีโอ 1600	0

ข้อมูลผลิตภัณฑ์:

อ่างอาบน้ำมีขนาดยาว 1600 มม. กว้าง 750 มม. และสูง 450 มม. ซึ่งผลิตจากวัสดุอะครีลิกเสริมใยแก้ว อ่างอาบน้ำติดตั้งแบบฝัง อ่างอาบน้ำนี้เหมาะสำหรับชุดแพททีโอ อ่างอาบน้ำพร้อมหมอนรองศีรษะ, ตะได้อ่างแบบป๊อปอัพและท่อน้ำล้น อ่างอาบน้ำรุ่นนี้คือ อ่างอาบน้ำโคห์เลอร์ รุ่น K-45699X-_____.

แพททีโอ 1600




ข้อมูลเฉพาะ

สุขภัณฑ์*:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	955 x 365 มม.
พื้นที่ด้านบน	1400 x 670 มม.
ระดับน้ำล้น:	
ระดับน้ำลึก	320 มม.
ความจุน้ำ	154 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2 นิ้ว)
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	21 กิโลกรัม
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย
250 กก./ตร.ม.

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์