


Features

- Acrylic and reinforced with fiberglass
- Drop-in
- Includes pillow head
- Includes pop-up drain and overflow
- Coordinates with Ove suite
- 1750 x 850 x 470 mm

BATH K-18256X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- IAPMO/UPC
- TIS 2141-2546

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-18256X	Ove plain bath	0

Product Specification:

The Ove bath shall be 1750 mm in length, 850 mm in width, and 470 mm in height. Bath shall be made of acrylic and reinforced with fiberglass. Bath shall be drop-in installation. Bath shall be coordinating Ove suite. Bath shall include pillow head, pop-up drain and overflow. th shall be Kohler Model K-18256X-_____.

OVE




Technical Information

Fixture*:	
Basin area:	
Basin area bottom	917 x 433 mm
Basin area top	1572 x 625 mm
To overflow:	
Water depth	327 mm
Capacity	283 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	25 kg
*Approximate measurements for comparison only.	

Installation Notes

Install this product according to the installation guide.
 Floor support under bath must provide for a minimum of 385 kg/square meter loading.

Dimensions are approximate.
 Unit: mm




Product Diagram

คุณลักษณะ

- อะครีลิกเสริมใยแก้ว
- แบบฝัง
- พร้อมหมอนรองศีรษะ
- พร้อมสื่อดูอ่างแบบป๊อปอัพและท่อน้ำล้น
- เหมาะสำหรับชุดโอฬ
- 1750 x 850 x 470 มม.

อ่างอาบน้ำ K-18256X



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z124.1.2
- IAPMO/UPC
- มอก. 2141-2546

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-18256X	อ่างอาบน้ำ รุ่น โอฬ	0

ข้อมูลผลิตภัณฑ์:

อ่างอาบน้ำโอฬมีขนาดยาว 1750 มม. กว้าง 850 มม. และสูง 470 มม. ซึ่งผลิตจากวัสดุอะครีลิกเสริมใยแก้ว อ่างอาบน้ำติดตั้งแบบฝัง อ่างอาบน้ำนี้เหมาะสำหรับชุดโอฬ อ่างอาบน้ำพร้อมหมอนรองศีรษะ, สื่อดูอ่างแบบป๊อปอัพและท่อน้ำล้น อ่างอาบน้ำรุ่นนี้คือ อ่างอาบน้ำ โคห์เลอร์รุ่น K-18256X-_____.

โอฬ




ข้อมูลเฉพาะ

สุขภัณฑ์*:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	917 x 433 มม.
พื้นที่ด้านบน	1572 x 625 มม.
ระดับน้ำล้น:	
ระดับน้ำลึก	327 มม.
ความจุน้ำ	283 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	25 กิโลกรัม
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย
385 กก./ตร.ม.

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์