


Features

- Acrylic and reinforced with fiberglass
- Drop-in
- Includes pillow head
- Includes pop-up drain and overflow
- Coordinates with Odeon suite
- 1800 x 900 x 480 mm

BATH K-18255X



Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- IAPMO/UPC
- TIS 2141-2546

Colors/Finishes

- 0: White

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Color/Finished
K-18255X	Odeon plain bath	0

Product Specification:

The Odeon bath shall be 1800 mm in length, 900 mm in width, and 480 mm in height. Bath shall be made of acrylic and reinforced with fiberglass. Bath shall be drop-in installation. Bath shall be coordinating Odeon Suite. Bath shall include pillow head, pop-up drain and overflow. Bath shall be Kohler Model K-18255X-_____.

ODEON


Technical Information

Fixture*:	
Basin area:	
Basin area bottom	1233 x 490 mm
Basin area top	1643 x 831 mm
To overflow:	
Water depth	340 mm
Capacity	296 liters
Drain hole	ø38 mm (1-1/2")
Overflow hole	ø52 mm
Weight	27 kg
*Approximate measurements for comparison only.	

Installation Notes

Install this product according to the installation guide.
 Floor support under bath must provide for a minimum of 400 kg/square meter loading.

Dimensions are approximate.
 Unit: mm




Product Diagram

คุณลักษณะ

- อะคริลิคเสริมใยแก้ว
- แบบฝัง
- พร้อมหมอนรองศีรษะ
- พร้อมสะดืออ่างแบบปีปอัฟและท่อน้ำล้น
- เหมาะสำหรับชุดโอดีออน
- 1800 x 900 x 480 มม.

อ่างอาบน้ำ K-18255X



มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ANSI Z124.1.2
- IAPMO/UPC
- มอก. 2141-2546

สี/วัสดุเคลือบผิว

- 0: สีขาว

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-18255X	อ่างอาบน้ำ รุ่น โอดีออน	0

ข้อมูลผลิตภัณฑ์:

อ่างอาบน้ำโอดีออนมีขนาดยาว 1800 มม. กว้าง 900 มม. และสูง 480 มม. ซึ่งผลิตจากวัสดุอะคริลิคเสริมใยแก้ว อ่างอาบน้ำติดตั้งแบบฝัง อ่างอาบน้ำนี้เหมาะสำหรับชุดโอดีออน อ่างอาบน้ำพร้อมหมอนรองศีรษะ, สะดืออ่างแบบปีปอัฟและท่อน้ำล้น อ่างอาบน้ำรุ่นนี้คือ อ่างอาบน้ำโคห์เลอร์รุ่น K-18255X-_____.

โอดีออน


ข้อมูลเฉพาะ

สุขภัณฑ์*:	
พื้นที่อ่างอาบน้ำ:	
พื้นที่ด้านล่าง	1233 x 490 มม.
พื้นที่ด้านบน	1643 x 831 มม.
ระดับน้ำล้น:	
ระดับน้ำลึก	340 มม.
ความจุน้ำ	296 ลิตร
รูท่อน้ำทิ้ง	Ø38 มม. (1-1/2")
รูท่อน้ำล้น	Ø52 มม.
น้ำหนัก	27 กิโลกรัม
*ระยะค่าโดยประมาณเพื่อการเปรียบเทียบเท่านั้น	

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งสุขภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง
พื้นที่ใช้รองรับอ่างอาบน้ำต้องสามารถรับน้ำหนักอย่างน้อย
400 กก./ตร.ม.

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์