


Features

- Brass valve bodies
- Quarter-turn washerless ceramic disc valves
- Flexible connections for easy installation
- Includes pop-up drain with lift rod and tailpiece
- 8" (203 mm) centers
- 140 mm spout reach
- Available with cross or lever handles

WIDESPREAD LAVATORY FAUCET K-14406



Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2067-2552



Colors/Finishes

- CP: Polished Chrome

Accessories:

- CP: Polished Chrome

Specified Model

Model	Description	Cross 	Lever 
K-14406-3	Purist widespread lavatory faucet, cross handles	CP	
K-14406-4	Purist widespread lavatory faucet, lever handles		CP

Product Specification:


The two-handle widespread lavatory faucet shall be made of brass valve bodies. Product shall feature quarter-turn washerless ceramic disc valves, flexible connections for easy installation, a 140 mm spout reach. Product shall be 8" (203 mm) centers. Product shall be available with cross or lever handles, and a pop-up drain with lift rod and tailpiece. Faucet shall be Kohler Model K-14406-____-CP.

PURIST

Installation Notes

Install this product according to the installation guide.

Dimensions are approximate.
Unit: mm.




Product Diagram

คุณลักษณะ

- ตัววาล์วทองเหลือง
- เซรามิกวาล์ว แบบหมุน 90 องศา
- ติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งได้ง่าย
- พร้อมสะดืออ่างแบบป๊อปอัพ
- เซ็นเตอร์ 8" (203 มม.)
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 140 มม.
- มือบิดแบบโครมหรือแบบก้านโยก

ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 8" K-14406



มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 2067-2552

สี/วัสดุเคลือบผิว

- CP: สีโครมเงา

ส่วนประกอบอื่นๆ:

- CP: สีโครมเงา

รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	แบบโครม	แบบก้านโยก
K-14406-3	ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 8" มือบิดแบบโครม รุ่น เพ็ญวิริส	CP	
K-14406-4	ก๊อกผสมอ่างล้างหน้า เซ็นเตอร์ 8" มือบิดแบบก้านโยก รุ่น เพ็ญวิริส		CP

ข้อมูลผลิตภัณฑ์:


ก๊อกผสมอ่างล้างหน้าแบบ 2 มือบิด ผลิตจากวาล์วทองเหลือง วาล์วก๊อกน้ำเป็นเซรามิกวาล์วแบบหมุน 90 องศา ก๊อกน้ำติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งได้ง่าย และมีระยะกึ่งกลางจากตัวก๊อกถึงปากก๊อก 140 มม. ก๊อกน้ำติดตั้งแบบเซ็นเตอร์ 8" (203 มม.) ก๊อกน้ำพร้อมสะดืออ่างแบบป๊อปอัพ พร้อมมือบิดแบบโครมหรือแบบก้านโยก ก๊อกน้ำรุ่นนี้คือ ก๊อกน้ำโคห์เลอร์รุ่น K-14406-____-CP

เพียวริส

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือข้อแนะนำการติดตั้ง

ขนาดระยะแสดงค่าโดยประมาณ
หน่วย: มม.



ภาพแสดงผลิตภัณฑ์

ก๊อกผสมอ่างล้างหน้าแบบเซ็นเตอร์ 8" รุ่น เพียวริส

หน้า 4/4

1106616-X4-A

KOHLER