

Features

- Brass construction
- One-piece, self-contained ceramic joystick valve actuation allows both volume and temperature control
- Flexible hose connection for easy installation
- Touch-activated drain
- Joystick lever handle
- 135 mm spout reach

Codes/Standards Applicable


Specified model meets or exceeds the following:

- TIS 2067-2552

Installation Notes

Install this product according to the installation guide.

SINGLE CONTROL LAVATORY FAUCET K-14660X




Specified Model

Model	Description	Color/Finished
K-14660X-4	Loure single control lavatory faucet	CP: Polished Chrome

Dimensions are approximate.

Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เซรามิคจอยสติ๊กวาล์ว วาล์วก่อนน้ำเดี่ยวควบคุมทั้งปริมาณน้ำและอุณหภูมิ
- ติดตั้งด้วยสายน้ำดี ทำให้ติดตั้งได้ง่าย
- พร้อมสะดืออ่างแบบกด
- มือบิดก้านโยกแบบจอยสติ๊ก
- ระยะจากกึ่งกลางตัวก๊อกถึงกึ่งกลางปากก๊อก 135 มม.


มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 2067-2552

ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมอ่างล้างหน้าแบบก้านโยก K-14660X




รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-14660X-4	ก๊อกผสมอ่างล้างหน้าแบบก้านโยก รุ่นลั้วร์	CP: สีโครมเงา

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์