

### WALL-MOUNT SHOWER VALVE-COLD WATER ONLY K-R99978T

#### Features

- Brass construction
- G1/2" connection
- Included ceramic disc valve
- Easy-sealant & free trim installation
- Lift and turn handle

#### Codes/Standards Applicable

Specified model meets or exceeds the following:

- N/A


#### Installation Notes

Install this product according to the installation guide.



#### Specified Model

Model	Description	Color/Finished
K-R99978T-4CD	Kumin wall-mount shower valve-cold water only	CP: Polished Chrome




**Flow Curve**

Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



#### Product Diagram

## วาล์วเปิด-ปิดน้ำเย็นแบบก้านโยก K-R99978T

### คุณลักษณะ

- ผลิตจากทองเหลือง
- เกสียวข้อต่อ G1/2"
- พร้อมเซรามิกวาล์ว
- ติดตั้งง่าย
- โยกและหมุนเพื่อใช้งาน

### มาตรฐาน

คุณสมบัติตามมาตรฐาน

- ไม่ระบุ


### ข้อสังเกตสำหรับการติดตั้ง

ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง



### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-R99978T-4CD	วาล์วเปิด-ปิดน้ำเย็นแบบก้านโยก รุ่นคูมิน	CP: สีโครมเงา




กราฟแสดงอัตราการไหล

หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 psi)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์