

EXPOSED WALL-MOUNT SHOWER MIXER K-45533X

Features

- Brass construction
- G1/2" connection
- Includes handshower with 1.5m hose
- Lever handle

Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552


Installation Notes

Install this product according to the installation guide.




Specified Model

Model	Description	Color/Finished
K-45533X-4	Cuff exposed wall-mount shower mixer	CP: Polished Chrome



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.
Unit: mm



Product Diagram

คุณลักษณะ

- ผลิตจากทองเหลือง
- เกลียวข้อต่อ G1/2"
- พร้อมหัวฝักบัวสายอ่อนและสายยาว 1.5 เมตร
- มือบิดแบบก้านโยก

มาตรฐาน

คุณสมบัติตามมาตรฐาน

- มอก. 2066-2552

ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

ก๊อกผสมเย็นอาบแบบติดผนัง พร้อมฝักบัวสายอ่อน K-45533X



รุ่นผลิตภัณฑ์


รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-45533X-4	ก๊อกผสมเย็นอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นคัพ	CP: สีโครมเงา



หมายเหตุ: อัตราการใช้ค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ

หน่วย: มม.



ภาพแสดงผลิตภัณฑ์