

### Features

- Brass construction
- G1/2" connection
- Water efficient flow control
- Includes handshower with 1.5 m hose
- Easy clean spray nozzles
- Ergonomic grip and use

### Codes/Standards Applicable

Specified model meets or exceeds the following:

- TIS 2066-2552

### Installation Notes


Install this product according to the installation guide.

## EXPOSED WALL-MOUNT SHOWER MIXER K-72351T



### Specified Model


Model	Description	Color/Finished
K-72351T-4	Aleo exposed wall-mount shower mixer	CP: Polished Chrome



Note: Flow rates are approximate. (1 gallon = 3.785 liters, 1 bar = 14.5 psi)

Dimensions are approximate.

Unit: mm



Note: The recommended dimension for installation can be adjusted according to user preferences and layout.

### Product Diagram

### คุณลักษณะ

- ผลิตจากทองเหลือง
- เกลียวข้อต่อ G1/2"
- กระแสน้ำคงที่
- พร้อมหัวฝักบัวสายอ่อนและสายยาว 1.5 เมตร
- หัวฝักบัวทำความสะอาดง่าย
- มือจับถูกต้องตามสรีรศาสตร์

### มาตรฐาน

- คุณสมบัติตามมาตรฐาน
- มอก. 2066-2552

### ข้อสังเกตสำหรับการติดตั้ง


ติดตั้งผลิตภัณฑ์โดยใช้คู่มือแนะนำการติดตั้ง

## ก๊อกผสมยืนอาบแบบติดผนัง พร้อมฝักบัวสายอ่อน K-72351T




### รุ่นผลิตภัณฑ์

รุ่น	ชื่อผลิตภัณฑ์	สี/วัสดุเคลือบผิว
K-72351T-4	ก๊อกผสมยืนอาบแบบติดผนังพร้อมฝักบัวสายอ่อน รุ่นอาเลโอ	CP: สีโครมเงา



หมายเหตุ: อัตราการไหลค่าโดยประมาณ (1 แกลลอน = 3.785 ลิตร, 1 บาร์ = 14.5 ปอนด์ต่อตารางนิ้ว)

ขนาดระยะแสดงค่าโดยประมาณ  
หน่วย: มม.



หมายเหตุ: ระยะแนะนำการติดตั้งสามารถปรับได้ตามความเหมาะสมของผู้ใช้งานและพื้นที่ติดตั้ง

### ภาพแสดงผลิตภัณฑ์