

## Features


- Multiple configuration options for opening widths from 30" (762 mm) to 72" (1829 mm)
- Walk through height of 75" (1905 mm)
- Available in 1/4" (6 mm) or 3/8" (10 mm) thick tempered glass
- Optional steam-sealing enclosure
- Easy adjustment for out-of-plumb conditions
- CleanCoat® glass coating for easy glass care and maintenance
- 3" (76 mm) width adjustment
- 1/2" (13 mm) height adjustment
- 3/8" (10 mm) out-of-plumb adjustment
- Sliding transom

## Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1 (tempered glass)
- CPSC 16CFR 1201 CAT II

## PIVOT STEAM SHOWER DOOR K-705801 ALSO K-705803, K-705805, K-705807



## Colors/Finishes

- SH: Bright Silver
- NX: Brushed Nickel
- ABV: Brushed Bronze

## Specified Model

Model	Description	Application	Glass Thickness	Frame Finishes/Colors		
K-705801-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705803-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705805-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705807-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705809-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705811-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705813-L	Pivot steam shower door	Shower	1/4" (6 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705815-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV
K-705817-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH	<input type="checkbox"/> NX	<input type="checkbox"/> ABV

## Product Specification

The pivot steam shower door shall offer multiple configuration options for opening widths from 30" (762 mm) to 72" (1829 mm). Product shall have pivot panel with a walk through height of 75" (1905 mm). Product shall be available in 1/4" (6 mm) or 3/8" (10 mm) thick tempered glass. Product shall have optional steam-sealing enclosure and CleanCoat™ glass coating for easy glass care and maintenance. Product shall be easy adjustment for out-of-plumb conditions. Product shall have 3" (76 mm) of width adjustment, 1/2" (13 mm) height adjustment, and 3/8" (10 mm) of out-of-plumb adjustment. Product shall have sliding transom. Pivot steam shower door shall be Kohler Model K-\_\_\_\_\_-\_\_\_\_\_.

Model	Description	Application	Glass Thickness	Frame Finishes/Colors
K-705819-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH <input type="checkbox"/> NX <input type="checkbox"/> ABV
K-705821-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH <input type="checkbox"/> NX <input type="checkbox"/> ABV
K-705823-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH <input type="checkbox"/> NX <input type="checkbox"/> ABV
K-705825-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH <input type="checkbox"/> NX <input type="checkbox"/> ABV
K-705827-L	Pivot steam shower door	Shower	3/8" (10 mm)	<input type="checkbox"/> SH <input type="checkbox"/> NX <input type="checkbox"/> ABV


## Installation Notes

Install this product according to the installation guide.

Recommended two person installation.

Model	A (Min-Max)	B (Min-Max)	C
<b>K-705801</b> <b>K-705815</b>	30" (762 mm) - 33" (838 mm)	20-1/4" (514 mm) - 23-1/4" (591 mm)	6-1/2" (165 mm)
<b>K-705803</b> <b>K-705817</b>	33" (838 mm) - 36" (914 mm)	20-1/4" (514 mm) - 23-1/4" (591 mm)	9-1/2" (241 mm)
<b>K-705805</b> <b>K-705819</b>	36" (914 mm) - 39" (991 mm)	23-1/4" (591 mm) - 26-1/4" (667 mm)	9-1/2" (241 mm)
<b>K-705807</b> <b>K-705821</b>	39" (991 mm) - 42" (1067 mm)	23-1/4" (591 mm) - 26-1/4" (667 mm)	12-1/2" (318 mm)
<b>K-705809</b> <b>K-705823</b>	45" (1143 mm) - 48" (1219 mm)	29-1/4" (743 mm) - 32-1/4" (819 mm)	12-1/2" (318 mm)
<b>K-705811</b> <b>K-705825</b>	57" (1448 mm) - 60" (1524 mm)	29-1/4" (743 mm) - 32-1/4" (819 mm)	24-1/2" (622 mm)
<b>K-705813</b> <b>K-705827</b>	69" (1753 mm) - 72" (1829 mm)	29-1/4" (743 mm) - 32-1/4" (819 mm)	36-1/2" (927 mm)

89" (2261 mm) Min  
89-1/2" (2273 mm) Max



## Product Diagram