

# Mira Vie

## Electric Shower



Consistent, all-year round, affordable performance



### Product Information

Description	Colour	Product No.
Mira Go 8.5kW	White/Chrome	1.1788.001
Mira Go 9.5kW	White/Chrome	1.1788.002

### Features & Benefits

#### Temperature control

Pressure stabilised temperature control

#### Easy to fit

Retrofits onto inlets of most Mira electric showers

Left-hand water and cable entry points

Dual terminal blocks

Adjustable slide bar fits over holes left by previous shower kit

#### Easy to service

Easy filter access

#### For your customer

Separate power and temperature controls.

Push button on/off

Eco setting saves water and energy

Mira Clearscale™ reduces limescale by up to 50%

Single spray showerhead with rub-clean nozzles

Modern aesthetics with chrome detailing

# Product Specification

## Tech Details

### Temperature control

Control type: Pressure stabilised

### Installation

Power options: 8.5kW 240V AC (7.8kW 230V AC) • 9.5kW 240V AC (8.7kW 230v AC)

Supply voltage: 230v ± 10%

Supply rating: 40 amp (8.5 & 9.5kW); 45 amp (10.8kW)

Terminal Block connections: Maximum 16mm<sup>2</sup>

Water entry points: Left (rising, falling & rear)

Cable entry points: Left (rising, falling & rear)

Inlet connections: 15mm plastic stub, compression or push-fit fittings

Outlet connections: ½" BSP Male

### Supply Conditions

Minimum maintained pressure: 8.5 & 9.5kW: 0.7 bar (7 metre head)

Maximum maintained pressure: 5.0 bar (50 metre head)

Maximum static pressure: 10.0 bar (100 metre head)

### Performance

Temperature stability: ± 6°C

### Safety Features

Phased shutdown: No

Factory set to safe max temp: No

Mira Sensi-flo™: No

### Accessories

Wide range of accessories available at [www.mirashowers.co.uk](http://www.mirashowers.co.uk)

### Approvals

Energy Efficiency: Class A



## Dimensions

