

STERLING®

A KOHLER COMPANY

Features

- Kit includes door, walls with corner caddy and 38" (96.5 cm) molded base
- Space-saving corner design
- Full length handle for easy operation
- Aluminum components extruded from alloy 6063-T5
- Tempered glass ensures maximum safety and durability
- Threshold directs water back into the shower and minimizes soap or lint build up
- Watertight flexible door magnet and seal
- Installs left- or right-handed
- Quick and easy to install with no track cutting required
- Convenient corner shelves to store shower supplies

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ANSI Z97.1 (tempered glass)


Specified Model

Model	Application	Glass Texture	Pattern	Color/Finishes (Frame/Base)
NI3190A-38*	Shower kit	Hammered	None	Refer to Price Book for additional colors/finishes
NI3196A-38*	Shower kit	Rain	None	
* Note: Add appropriate frame finish/base and wall color code to the end of the unit model # when ordering				

Included Components	Description
K2510-SW (White) or K2510-A (Almond)	Thermoformed Styrene Wall Surround
I3838N-W (White) or I3838N-A (Almond)	Polypropylene Receptor only
7360000	2" (5.1 cm) shower drain, chrome
Note: Reference individual specification sheets for I3838N-___ receptor and K2510-___ wall dimensions	

NEO-ANGLE ECONOMY SHOWER KIT

NI3190A
ALSO NI3196A




Colors/Finishes

- Refer to the Price Book for current frame finish and glass options

Technical Information

Model	A	B	C	D (Height)	E (Walk Through Max)
NI3190A-38*	18-1/4" (46.4 cm)	25-1/4" (64.1 cm)	38" (96.5 cm)	72" (182.9 cm)	22" (55.9 cm)
NI3196A-38*	18-1/4" (46.4 cm)	25-1/4" (64.1 cm)	38" (96.5 cm)	72" (182.9 cm)	22" (55.9 cm)

***Note: Add appropriate frame finish/base and wall color code to the end of the unit model # when ordering**



Product Diagram