

# STERLING<sup>®</sup>

A KOHLER COMPANY

## S P E C I F I C A T I O N S

## Finesse™ Bypass Tub Doors Series 5100/5300

### Standard Features


- Heavy-duty, anodized aluminum-framed sliding glass doors
- Out-of-plumb adjustability allows for easy installation
- Easy-to-clean track with guide system
- 5/32" thick tempered glass
- Frame components extruded from aluminum alloy 6063-T5
- All necessary hardware included

### Standards and Ratings


- Tempered glass complies with ANSI Z97.1-1984 and Architectural Glazing Standard 16CFR1201

### Optional Features

- Available with framed or frameless doors
- Available in two heights (58 5/16" or 55 3/4")
- Silver or polished brass frame finishes
- Frameless models available in clear glass
- Choose from five glass patterns for framed models:
  - Clear with etched oval pattern
  - Pebble
  - Rain
  - Fluted
  - V-grooved



Model 5108



Model 5106

### Features

#### Tempered glass

#### Exclusive roller system

#### Designer towel bars

#### Interchangeable top track

#### Stainless steel hardware

### Benefits

Tempered glass offers maximum safety and durability. Rounded edges on frameless doors eliminate sharp corners.

Unique top track roller system and continuous contact bottom track with pile insert mean smooth, silent operation.

Two attractively styled towel bars enhance appearance and usability—both inside and outside the tub.



Top track can be installed with either the round side out for a contemporary look or the flat side out for a more traditional look.

Prevents fasteners from rusting or corroding in a damp environment.

# Finesse™ Bypass Tub Doors Series 5100/5300



## D I M E N S I O N S

Series 5100




SECTION A - A

Series 5300



SECTION A - A



| Model     | Frame Finish   | Framed/<br>Frameless | Glass Panel Pattern | Door Height                       | Max. Opening                     |
|-----------|----------------|----------------------|---------------------|-----------------------------------|----------------------------------|
| 5100-59S  | Silver         | Framed               | Pebble Glass        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5100-59PB | Polished Brass | Framed               | Pebble Glass        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5101-59S  | Silver         | Framed               | V-Grooved Glass     | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5101-59PB | Polished Brass | Framed               | V-Grooved Glass     | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5106-59S  | Silver         | Framed               | Rain Glass          | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5106-59PB | Polished Brass | Framed               | Rain Glass          | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5107-59S  | Silver         | Framed               | Oval Pattern        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5107-59PB | Polished Brass | Framed               | Oval Pattern        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5108-59S  | Silver         | Framed               | Fluted Glass        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5108-59PB | Polished Brass | Framed               | Fluted Glass        | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5120-57S  | Silver         | Framed               | Pebble Glass        | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5120-57PB | Polished Brass | Framed               | Pebble Glass        | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5126-57S  | Silver         | Framed               | Rain Glass          | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5126-57PB | Polished Brass | Framed               | Rain Glass          | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5127-59S  | Silver         | Framed               | Oval Pattern        | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5127-59PB | Polished Brass | Framed               | Oval Pattern        | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5305-59S  | Silver         | Frameless            | Clear Glass         | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5305-59PB | Polished Brass | Frameless            | Clear Glass         | 58 <sup>5</sup> / <sub>16</sub> " | 59 <sup>5</sup> / <sub>8</sub> " |
| 5325-57S  | Silver         | Frameless            | Clear Glass         | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |
| 5325-57PB | Polished Brass | Frameless            | Clear Glass         | 55 <sup>3</sup> / <sub>4</sub> "  | 57"                              |



★ Made in U.S.A.