

# KOHLER® 7000 SERIES™

20–26 HP Engines



KOHLER®

**KOHLER.**  
7000 Series **PRO**  
Premium Air Filter  
**26**<sub>hp</sub>  
KT745-747  
Flowed at 3000 rpm over 54" x 27" x 40" Grits  
62 712 187

**KOHLER**®  
IN POWER. SINCE 1920.

# A V-TWIN BEAST FOR BACKYARD WARRIORS.

Now with a 3-year warranty.



Power up your tractor or ZTR with the air-cooled, V-twin 7000 Series™ engine, and run rings around your neighbors with pro-grade features, easy starts, durable components and powerful cuts.

## BUILT TO LAST

- Based on KOHLER Command PRO® commercial engine design
- Pressure lubrication extends engine life by keeping critical components well-lubricated
- Upgradable oil and fuel filters provide extra protection from dirt
- Air filter options available—HD air filter is 2x larger to keep more debris out, and PRO air filter offers commercial-grade filtration and longer maintenance intervals

## POWER WHEN YOU NEED IT

- Consistent-Cut™ technology maintains engine speed for a cleaner turf cut—so your lawn looks great even in tough mowing conditions

## JUST TURN THE KEY AND GO

- Reliable starting, hot or cold, even at temperatures below freezing with Smart-Choke™ technology
- No need to choke the engine—starts at any throttle position
- Adds just the right amount of fuel during starting

## THE BRAND YOU TRUST

- Built to last since 1920
- Engineered and assembled in the U.S.A.
- Limited 3-year consumer warranty
- With PRO air filter option: 1-year, unlimited-hour limited commercial warranty

For more information, contact your KOHLER source of supply. Kohler Co. reserves the right to make modifications without prior notice.

**KOHLER**  
IN POWER. SINCE 1920.

**KOHLERENGINES.COM**

Printed in Italy ED0035585290 Rev.01 06/18 Eng KOHLER CO.