


FEATURES

- Brass valve body
- Pressure-balancing mechanism of one-piece diaphragm cartridge design for ease of maintenance
- Mixing valve cycles from "cold" to "hot"
- 3/4" NPT connections
- High-Temperature limit stop
- Integral shut-off valve stops
- Minimum operating pressure 15 psi (103.4 kPa)

CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- ASSE 1016



INSTALLATION NOTES

Install this product according to the installation guide. Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

SPECIFIED MODEL

Model	Description	Finishes
P29306-WS	High Flow Pressure Balance Rough-In Assembly	<input type="checkbox"/> NA

We reserve the right to make revisions without notice in the design of products or in packaging unless this right has specifically been waived at the time the order is accepted.