KALLISTA

1/2" Volume Control Valve 3/4" Volume Control Valve

FEATURES


- Forged brass valve body
- Single-handle temperature control
- Quarter-turn washerless ceramic disc valves
- 1/2" or 3/4" NPT connections
- Intended for use with KALLISTA thermostatic mixer valving
- **P29527:** 10.0 gal/min (37.9 l/min) maximum flow rate at 45 psi (310.3 kPa)
- **P29528:** 28.0 gal/min (106.0 l/min) maximum flow rate at 45 psi (310.3 kPa)

CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:

ASME A112.18.1/CSA B125.1

P29527, P29528



	А	В	С
P29527-00	1/2" NPT	3" (76 mm)	4" (102 mm)
P29528-00	3/4" NPT	3-3/16" (81 mm)	4-1/8" (105 mm)

INSTALLATION NOTES		
Install this product according to the installation guide.		

SPECIFIED MODEL			
Model	Description	Finishes	
P29527-00	1/2" Volume Control Valve	□ NA	
P29528-00	3/4" Volume Control Valve	□ NA	

We reserve the right to make revisions without notice in the design of products or in packaging unless this right has specifically been waived at the time the order is accepted.