














				_	1/8" 1/4" 5/16"
Record your model number below for future reference:	CAUTION: Risk of personal injury.  Do not install where the product might be used as a grab or support bar.	Important Information These products should be located and mounted to a wall stud. While it is possible to mount them to any surface, a stud-mounted product will yield the best results.	Recommended Tissue Holder Location	1 Two-Post Accessories:  Verify "X" against the measurements of your product model.  P30575: 12" (305 mm) P30576: 18" (457 mm)	2 For All Installations: Loosen the setscrew and remove the wall plate from the accessory.
			8" (203 mm) – 12" (305 mm) 6" (152 mm)	X X X	
3 Single-Post Accessories:  Position the wall plate and mark the holes. Verify level.	4 Drywall Into Studs: Drill 1/8" holes. Secure the wall plate(s).	Drywall Between Studs: Drill 5/16" holes. Use the provided pin to install the drywall anchors. Secure the wall plate(s).	Ceramic Tile:  Drill 1/4" holes. Insert ceramic anchors.  Secure the wall plate(s).	5 For All Accessories: Slide the accessory onto the post(s). Tighten the setscrew(s).	



1340951-2-**A** © 2018 KALLISTA