

## Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 7-3/16" (183 mm)
- Required rough-in sold separately
- Diverter, handshower, and handshower trim sold separately
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

## Required Products/Accessories

P19303-00 3/4" Ceramic High-Flow Valve System

## Recommended Products/Accessories

P50047-G5 Small Rectangular Air Bathtub  
P24843-00 Wand Dual-Function Handshower with Hose  
P21930-00 Drain Trim Kit  
P34402-00 Towel Bar, 18"



**ADA** **CSA B651** **OBC**

## Codes/Standards

ASME A112.18.1/CSA B125.1

ADA

ICC/ANSI A117.1

CSA B651

OBC

IAPMO Certification


## KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	GN	Gunmetal
	BL	Matte Black
	ULB	Unlacquered Brass
	BN	Brushed Nickel
	BAF	Brushed French Gold
	SN	Polished Nickel



## Technical Information

All product dimensions are nominal.

### Faucet:

Flow rate: 9.98 gal/min (37.8 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: No

### Spout:

Spout reach: 7-3/16" (183 mm)

## Notes

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.