

## Features

- A selection of products within this collection is in stock and ready to ship. Please visit [kallista.com/readytoship](http://kallista.com/readytoship) for the complete list of Ready-to-Ship products and finishes
- High-quality solid-brass construction for durability and reliability
- Easy-to-clean sprayface resists mineral buildup
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Sprayhead pivots 25 degrees
- Features an internal volume control for complete shut-off
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

## Recommended Products/Accessories

- P21664-00 Modern Slidebar
- P21501-00 Showerhead with Arm



## Codes/Standards

ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
IAPMO Certification

## KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.


## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome
	GN	Gunmetal
	BL	Matte Black
	W7	Black Nickel
	SN	Polished Nickel
	AF	French Gold
	BAF	Brushed French Gold
	BN	Brushed Nickel

# KALLISTA.

Foundations  
Body Spray  
P22078-00



## Technical Information

All product dimensions are nominal.

Drain included: No

Drain with  
overflow: No