

Features

- Ready-to-Ship (RTS) Program, in-stock and ready for immediate shipment: Polished Chrome (CP), Nickel Silver (AD)
- Required shower arm sold separately (P24762-00-* or P24763-00-CP)
- High-quality solid brass construction for durability and reliability
- Single function spray
- Easy to clean sprayface resists mineral buildup
- WaterSense and CEC compliant with a maximum flow rate of 1.75 gpm (6.6 lpm)
- Wall-mount installation

Required Products/Accessories

P24762-00

Recommended Products/Accessories

P24761-00 Handshower with Hose
P24715-LV
P22079-00
P21515-00

Codes/Standards

ASME A112.18.1/CSA B125.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome
	AG	Brushed Nickel
	W7	Black Nickel
	24K	Polished Gold
	AF	French Gold
	SN	Polished Nickel
	BV	
	BAF	Brushed French Gold

Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Showerhead/Body Spray:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

Pressure: 80 psi (5.5 bar)

Pressure/fixture Supply Requirements

Min flow rate: 1.75 gpm (6.6 lpm)

Notes

For use with automatic compensating valves rated at 1.05 gal/min (4 l/min) or less.