

Features

- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/readytoship for the complete list of Ready-to-Ship products and finishes
- Two spray options available (wide coverage spray, concentrated spray)
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Includes 59" (1499 mm) hose
- Handshower mounts to deck or wall with your choice of required installation mounting hardware (sold separately)
- 1.5 gpm (5.7 lpm) option available for projects
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

Recommended Products/Accessories

- P21661-00 Contemporary Wall Supply Elbow
- P24453-00 Wall Bracket
- P24482-00 Showerhead with Arm
- P31425-00 Towel Bar, 24"

Optional Products/Accessories



Codes/Standards

- ASME A112.18.1/CSA B125.1
- ASSE 1014
- DOE - Energy Policy Act 1992
- EPA WaterSense®
- California Energy Commission (CEC)
- OBC


KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BZ	Antique Bronze
	GN	Gunmetal
	BL	Matte Black
	LB	Bronze
	W6	Weathered Bronze
	W7	Black Nickel
	ULB	Unlacquered Brass
	BN	Vibrant® Brushed Nickel



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

OBC compliant when installed to the specific requirements of these regulations.