

Features

- High-quality solid-brass construction for durability and reliability
- Required shower arm sold separately
- 2.5 gpm (9.5 lpm) maximum flow rate
- Single-function spray
- Includes escutcheon
- Air-induction technology maximizes the air/water mix for a powerful, even flow
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

Required Products/Accessories

P21520-00 Rain Showerhead Arm

or

P21521-00 Rain Showerhead Arm

or

P21522-00 Rain Showerhead Arm

or

P21523-00 Wall-Mount Rain Showerhead Arm



Codes/Standards









ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
IAPMO Certification

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	BN	Brushed Nickel
	SN	Polished Nickel
	BAF	Brushed French Gold
	BV	Brushed Bronze
	AF	French Gold

KALLISTA®

Foundations by KALLISTA
Air-induction oversized contemporary rain
showerhead
P26139-00



Technical Information

All product dimensions are nominal.

Drain included: No

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Pressure: 80 psi (5.5 bar)