

KALLISTA®

One™ by KALLISTA Single-control bidet faucet P26614-00

Features

- High-quality solid metal construction for durability and reliability
- Swivel spray aerator
- Spout reach is 4-7/8" (124 mm)
- 6-11/16" (170 mm) faucet height
- 1.5 gpm (5.7 lpm) minimum flow rate at 20 psi (1.4 bar)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Single-hole installation
- Unlacquered Brass (ULB) available in North America and the United Kingdom only



Recommended Products/Accessories

- P24409-00 Single-control sink faucet
- P34408-00 Toilet Paper Holder
- P34410-00 Towel Ring
- P74053-00

Codes/Standards







ASME A112.18.1/CSA B125.1
IAPMO Certification

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	SN	Polished Nickel
	BAF	Brushed French Gold
	BN	Brushed Nickel

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

6-11-2024 20:03 - US



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 20 psi (1.4 bar)

Drain included: Yes

Spout:

Spout reach: $4\text{-}7/8"$ (124 mm)

Handshower:

Rated maximum flow: 1.5 gal/min (5.7 l/min)

Notes

Install this product according to the installation instructions.