

Features

- High-quality solid-brass construction for durability and reliability
- Wall-mount installation
- 22" (559 mm) reach capability

Recommended Products/Accessories

P25202-LV Deck-Mount Bridge Kitchen Faucet, Lever Handles
P25205-00 Bar Faucet
L20312-00 30" Butler Sink
P30801-00 4" cabinet pull



Codes/Standards






ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
IAPMO Certification


KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	SN	Polished Nickel
	BN	Brushed Nickel



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 3.2 gal/min (12.1 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Notes

Install this product according to the installation instructions.