

# KALLISTA®

## 002™ by KALLISTA Freestanding, floor-mount bath faucet, less handshower P34127-LV

### Features

- High-quality metal construction for durability and reliability
- Floor-mount, single hole installation
- Required mounting block sold separately (P20511-00-NA)
- Required handshower sold separately
- 10-3/4" (273 mm) spout reach
- 38-3/16" (970 mm) total faucet height
- 37-1/8" (943 mm) spout height
- Includes integral valve
- Includes hardware kit and escutcheon

### Required Products/Accessories

For freestanding installation  
P20511-00

or

P24843-00 Wand Dual-Function Handshower with Hose

### Recommended Products/Accessories

P50206-00 Freestanding Bathtub

P34137-00 Towel Bar, 24"

P34139-00 002™ Hook



### Codes/Standards

ASME A112.18.1/CSA B125.1






IAPMO Certification

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty  
information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	SN	Polished Nickel
	BAF	Brushed French Gold
	BN	Brushed Nickel

---

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

6-11-2024 21:04 - US

# KALLISTA

002™ by KALLISTA  
Freestanding, floor-mount bath faucet, less  
handshower  
P34127-LV



## Technical Information

All product dimensions are nominal.

### Faucet:

Flow rate: 7 gal/min (26.5 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: No

### Spout:

Spout reach: 10-3/4" (273 mm)

## Notes

Install this product according to the installation guide.