

KALLISTA®

KALLISTA Round Contemporary Showerhead with Arm P34135-00

Features

- Air-induction technology maximizes the air/water mix for a powerful, even flow
- 1.75 gpm (6.6 lpm) maximum flow rate
- High quality full brass construction for durability and reliability
- Single-function spray
- Easy-to-clean sprayface resists mineral buildup
- Wall-mount installation
- Unlacquered Brass (ULB) available in North America and the United Kingdom only



Recommended Products/Accessories

- P34130-LV Single Control trim, lever handle
- P34131-LV Single Control trim with diverter, lever handle
- P34132-LV Thermostatic trim, lever handle
- P34134-LV Volume Control Trim, Lever Handle
- P34133-LV Transfer Trim, Lever Handle
- P21513-00 Air-Induction Large Contemporary Rain Showerhead
- P24843-00 Wand Dual-Function Handshower with Hose



Codes/Standards









- ASME A112.18.1/CSA B125.1
- DOE - Energy Policy Act 1992
- EPA WaterSense®
- California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	ULB	Unlacquered Brass
	BAF	Brushed French Gold
	SN	Polished Nickel
	AF	French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

6-11-2024 21:02 - US

KALLISTA®

KALLISTA
Round Contemporary Showerhead with Arm
P34135-00



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 1.75 gal/min (6.6 l/min)

Pressure: 45 psi (3.1 bar)

Notes

Install this product in accordance with the installation instructions.