

KALLISTA®

Perfect
Under-mount Sink, Centric Rectangle w/ Overflow,
Glazed
P74236-WO

Features

- Ready-to-Ship (RTS) Program, in-stock and ready for immediate shipment
- Constructed of Vitreous China
- 19-13/16" (503 mm) total width
- 15-7/16" (392 mm) total length
- 6-7/8" (175 mm) total depth
- Includes mounting hardware
- Built-in overflow
- ADA compliant
- Glazed underside

Recommended Products/Accessories

P26100-CU
P26001-LV
P21688-00 Bottle Trap
P21644-00 Valve Shroud

ADA

Codes/Standards

ASME A112.19.2/CSA B45.1

ADA

ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

KALLISTA

Perfect
Under-mount Sink, Centric Rectangle w/ Overflow,
Glazed
P74236-WO

Technical Information

All product dimensions are nominal.

Bowl configuration:	Single
Installation:	Undermount
Bowl area:	Length: 17-5/16" (440 mm) Width: 13" (330 mm) Bowl depth: 6-7/8" (175 mm) Water depth: 4" (102 mm)
Drain hole:	1-3/4" (44 mm)

Notes

Install this product according to the installation instructions.

ADA compliant when installed to the specific requirements of these regulations.