

KALLISTA®

Vir Stil® Minimal Single-handle bar sink faucet P80270-00

Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 5-9/16" (141 mm)
- 1.5 gpm (5.7 lpm) maximum flow rate
- Single-hole installation

Recommended Products/Accessories

L20311-00 24" Butler Sink
P25517-00 Pull-Down Kitchen Faucet
P34000-00 Sink strainer



ADA

CSA B651

Codes/Standards




ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
IAPMO Certification

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	VS	Stainless
	SN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

6-23-2024 21:13 - US

KALLISTA

Vir Stil® Minimal
Single-handle bar sink faucet
P80270-00



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Spout:

Spout reach: 5-9/16" (141 mm)

Notes

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

6-23-2024 21:13 - US