

Features

- Rounded oak doors with curved metal edge detail
- Stainless steel sleigh legs
- Solid stainless steel door pulls
- Internal storage shelf
- Internal storage drawer with integrated handle
- Removable glass drawer dividers included

Materials & Construction


- Solid wood and veneer construction
- Stainless steel sleigh legs
- Full plywood back panel, no cutout
- Dovetailed drawers with solid oak front
- Blum undermount full extension slow close slide
- Blum slow close door hinges
- Durable, moisture resistant polyurethane finish
- Adjustable leveling feet

Options

- Available in:
 CVBE3621587, Matte Black Oak paired with Aged Brass
 CVBE3620169, Natural Grey paired with Brushed Pewter
- Engineered stone tops available:
 TA36UCO93-8CS2
 TA36UCO95-8CS2
 TA36UCO96-8CS2
 TA36UCO97-8CS2
 TA36UCO98-8CS2
 TA36UCO99-8CS2
 TA36UCO100-8CS2
 TA36UCO101-8CS2
- Coordinating mirrors available




Dimensions

Width: 35-7/8"
 Height: 32-7/8"
 Depth: 22-7/8"



Model Number Key

PRODUCT LINE	CATEGORY	COLLECTION	WIDTH	FINISH OPTIONS	OPTIONS
C = Craft Series	V = Vanity	BE = Bergman	36"	(See above)	(See above)



Internal Construction

Features

- Silestone Quartz Surface
- Includes Robern Ceramic Lavatory
- Includes installation hardware

Materials & Construction


- Pre-drilled for 8" wide spread faucet

Options

- Available finishes:
 - 93, White Zeus Extreme
 - 95, Eternal Marquina
 - 96, Pietra
 - 97, Calypso
 - 98, Eternal Serena
 - 99, Silken Pearl
 - 100, Eternal Calcatta Gold
 - 101, Iconic Black
- Pairs with Craft Series Chestnut Hill, Bergman, Sendai, and Mackey 36" vanities

Dimensions

Width: 36"
 Height: 1-1/8"
 Depth: 23"



Model Number Key

CATEGORY	DEPTH	WIDTH	LAV TYPE	OVERFLOW	COLORS	DASH	FAUCET HOLES	OPTIONS
T = Top	A = 23" Depth Fabricated Top	36"	U = Under Counter	C = Center Mounted	(See above)	-	8 = 3 Holes Drilled (Centered on Lav Location)	(See above)

36" Top TA36UCOXXX-8CS2

